

Cable de 3m DVI-I Monomodo Macho a Macho para Monitor Single Link - Cable DVI digital y Análogo de Modo Único

ID del Producto: DVIISMM10



The DVIISMM10 DVI-I Single Link cable features 2 male DVI (23-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 10ft DVI-I male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Connect your desktop or laptop computer to a DVI-I Single Link display or projector

Características

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec

- Aluminum-Mylar Foil with Braided Shielding
- Soporta hot plugging de dispositivos de vídeo DVI
- Compatible con los Estándares DVI DDWG
- Supports both analog and digital displays

Hardware

Política de Garantía	Lifetime
Estándares Industriales	DVI DDWG Standard

Rendimiento

Tasa de Transferencia de Datos Máxima	4.95 Gbits/sec
---------------------------------------	----------------

Conector(es)

Conector A	1 - DVI-I (23 pines)
Conector B	1 - DVI-I (23 pines)

Características Físicas

Color	Negro
Calibre del Conductor	28 AWG
Longitud del Cable	10.0 ft [3.0 m]

Información de la Caja

Cantidad de Paquetes	1
Longitud de la Caja	5.7 in [14.4 cm]
Ancho de la Caja	1.0 in [24.7 mm]
Altura de la Caja	11.0 in [28 cm]
Peso (de la Caja) del Envío	1.1 lb [0.5 kg]

Contenido de la Caja

Incluido en la Caja

1 - 10 ft DVI-I Single Link Digital Analog Monitor Cable
M/M

Información Acerca
de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.