

10 ft DVI-I Single Link Digital Analog Monitor Cable M/M

Productcode: DVIISMM10



The DVIISMM10 DVI-I Single Link cable features 2 male DVI (23-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 10ft DVI-I male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Connect your desktop or laptop computer to a DVI-I Single Link display or projector

Eigenschappen

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Ondersteunt hot-plugging van DVI-beeldschermen

- Voldoet aan de DVI DDWG-specificaties
- Supports both analog and digital displays

Hardware

Garantiebeleid	Lifetime
Industriestandaarden	DVI DDWG Standard

Prestaties

Maximale overdrachtsnelheid	4.95 Gbits/sec
-----------------------------	----------------

Connector(en)

Connector A	DVI-I (23-polig)
Connector B	DVI-I (23-polig)

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	10.0 ft [3.0 m]

Verpakkingsinformatie

Package Length	5.7 in [14.4 cm]
Package Width	1.0 in [24.7 mm]
Package Height	11.0 in [28 cm]
Verzendgewicht (verpakt)	17.3 oz [490 g]

Wat wordt er meegeleverd

Meegeleverd	10 ft DVI-I Single Link Digital Analog Monitor Cable M/M
-------------	--

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.