

15 ft DVI-I Single Link Digital Analog Monitor Cable M/M

Product ID: DVIISMM15



The DVIISMM15 DVI-I Single Link cable features 2 male DVI (23-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 15ft DVI-I male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-I Single Link display or projector

Features

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

- Supports both analog and digital displays

Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

Performance

Maximum Data Transfer Rate	4.95 Gbits/sec
----------------------------	----------------

Connector(s)

Connector A	DVI-I (23 pin)
Connector B	DVI-I (23 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	15.0 ft [4.6 m]

Packaging Information

Package Length	9.7 in [24.6 cm]
Package Width	1.3 in [34 mm]
Package Height	12.4 in [31.5 cm]
Shipping (Package) Weight	23.3 oz [660 g]

What's in the Box

Included in Package	15 ft DVI-I Single Link Digital Analog Monitor Cable M/M
---------------------	--

**Product appearance and specifications are subject to change without notice.*

