

## 6 ft DVI-I Single Link Digital Analog Monitor Cable M/M

**Product ID:** DVIISMM6



The DVIISMM6 DVI-I Single Link cable features 2 male DVI (23-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 6ft DVI-I male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

### **Certifications, Reports and Compatibility**

### **Applications**

- Connect your desktop or laptop computer to a DVI-I Single Link display or projector

### **Features**

- Supports a maximum resolution of 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

- Supports both analog and digital displays

---

#### Hardware

Warranty	Lifetime
Industry Standards	DVI DDWG Standard

---

#### Performance

Maximum Data Transfer Rate	4.95 Gbits/sec
----------------------------	----------------

---

#### Connector(s)

Connector A	DVI-I (23 pin)
Connector B	DVI-I (23 pin)

---

#### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	9.8 oz [278 g]

---

#### Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.9 in [24 mm]
Shipping (Package) Weight	10.1 oz [287 g]

---

#### What's in the Box

Included in Package	6 ft DVI-I Single Link Digital Analog Monitor Cable M/M
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

