

## 18in DVI-D Single Link Cable - M/M

**Product ID:** DVIMM18IN

The DVIMM18INDVI-D Single Link cable features 2 male DVI (19-pin) connectors and offers 18 inches in cable length, making it perfect for shorter connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 18in DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

## Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

<b>Hardware</b>	Warranty	Lifetime
	Industry Standards	DVI DDWG Standard
<b>Performance</b>	Maximum Data Transfer Rate	4.95 Gbits/sec
<b>Connector(s)</b>	Connector A	DVI-D (19 pin)
	Connector B	DVI-D (19 pin)
<b>Physical Characteristics</b>	Color	Black
	Wire Gauge	28 AWG
	Cable Length	18.0 in [4.6 cm]
	Product Length	18.0 in [4.6 cm]

Product Width	1.6 in [40 mm]
Product Height	0.6 in [15 mm]
Weight of Product	3.3 oz [94 g]

---

**Packaging Information**

Package Length	8.7 in [2.2 cm]
Package Width	7.9 in [2 cm]
Package Height	0.7 in [17 mm]
Shipping (Package) Weight	3.6 oz [103 g]

---

**What's in the Box**

Included in Package	18in Single Link LCD Flat Panel Monitor DVI-D Cable - M/M
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*

