

3 ft DVI-D Single Link Cable - M/M

Product ID: DVIMM3

The DVIMM3 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and offers 3 feet in cable length, making it perfect for shorter connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 3ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- Supports hot-plugging of DVI display devices
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Compliant with DVI DDWG Standards
- Aluminum-Mylar Foil with Braided Shielding

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	DVI-D (19 pin)
Connector B	DVI-D (19 pin)

Physical



Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Product Width	1.6 in [39.6 mm]
Product Height	0.6 in [16.0 mm]
Weight of Product	4.3 oz [121.0 g]

Packaging Information

Package Quantity	1
Package Length	7.9 in [20.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	4.6 oz [131.0 g]

What's in the Box

Included in Package	3 ft DVI-D Single Link Cable - M/M
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***

