

1 ft DVI-D to DVI-D & HDMI Splitter Cable - M/F

Productcode: DVISPL1DH



This 1ft DVI to DVI+HDMI Splitter Cable splits the digital DVI signal output by a computer or satellite receiver into one DVI and one HDMI output, allowing you to view content on one DVI display and one HDMI display simultaneously.

Backed by lifetime warranty, our DVI to DVI + HDMI splitter cable offers guaranteed durability and reliability.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Ideal for use LCD TV, LCD Projectors, Plasma TV, HDTV and DVD Player and set-top box
- This DVI-D splitter cable makes things easy with being able to instantly connect 1-DVI-D and 1-HDMI displays to a single digital DVI source

Eigenschappen

- Compatible with computers and HDTV video sources (satellite receivers, DVD players, etc) with DVI outputs

- Support for high-resolution images
- Lifetime warranty and FREE LIFETIME tech support

Prestaties

Garantiebeleid	Lifetime
Maximale digitale resoluties	2560 × 1600 @ 60Hz

Connector(en)

Connector A	1 - DVI-D (25-polig)
Connector B	1 - DVI-D (25-polig)
	1 - HDMI (19-polig)

Speciale opmerkingen / vereisten

Notitie	This product will split your video signal to deliver two identical images of the same resolution. It cannot be used to span an image across two displays, or to show different images on each display.
---------	--

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	1.0 ft [0.3 m]
Lengte product	12.0 in [30.5 cm]
Breedte product	0.0 in [0.0 cm]
Hoogte product	0.0 in [0.0 cm]
Gewicht product	5.0 oz [141.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.9 in [22.5 cm]

Package Width	4.9 in [12.5 cm]
Package Height	1.9 in [4.7 cm]
Verzendgewicht (verpakt)	5.2 oz [146.0 g]

Wat wordt er
meegeleverd

Meegeleverd	1 - 1 ft DVI-D to DVI-D & HDMI Splitter Cable - M/F
-------------	---

Garantiebepalinge
n

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.