

3m DVI to VGA Display Monitor Cable M/M - DVI to VGA (15 Pin)

Produkt ID: DVIVGAMM3M



The DVIVGAMM3M DVI to VGA Display Monitor Cable (3m) features a DVI-A male connector and a VGA male connector, enabling you to connect a VGA display to a PC or Mac® computer with a DVI-I analog output.

Expertly designed and constructed of only high quality materials, the DVI-A to VGA cable is backed by StarTech.com's Lifetime Warranty.

## Certifikat, rapporter och kompatibilitet

### Användning

- Connect a VGA display to a PC or Mac® with a DVI Analog Video Card

### Funktioner

- DVI-A (Male) to VGA (Male) Connectors
- High quality shielding prevents EMI interference
- Compliant with DVI DDWG Standards
- Molded connector ends with strain relief
- Gold plated contacts for maximum conductivity

- Triple coaxial + twisted-pair wire for crystal clear display

---

#### Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

---

#### Kontakt(er)

Connector A	DVI-A (17-stifts)
Connector B	VGA (15-stifts, High Density D-Sub)

---

#### Utseende

Färg	Svart
Tråddimension	28 AWG
Kabellängd	9.8 ft [3 m]
Produktlängd	9.8 ft [3.0 m]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	8.9 oz [252.0 g]

---

#### Förpackning

Förpackningsantal	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.3 in [34.0 mm]
Fraktvikt (förpackning)	9.2 oz [260.0 g]

---

#### Vad det är i lådan

Ingår i paketet	3m DVI to VGA Display Monitor Cable
-----------------	-------------------------------------

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

