

6 ft DVI to Coax High Resolution VGA Monitor Cable

Produkt-ID: DVIVGAMM6



The DVIVGAMM6 6-foot DVI to VGA Monitor Cable features a DVI (analog) male connector and a VGA (High Density D-Sub) male connector, providing a cost-effective way to connect an analog or a dual mode Flat Panel Display to a PC or Mac® computer with a DVI Analog Video Card.

Expertly designed and constructed of only high quality materials, the 6ft DVI to VGA Monitor cable is backed by StarTech.com's Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connects PC/Mac® with DVI Analog Video Card to an Analog or Dual-Mode Flat Panel Display

Merkmale

- Manufactured according to DVI specifications
- Molded connector ends with strain relief

Hardware

Garantiebestimmungen	Lifetime
Active or Passive Adapter	Passiv
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Steckverbinder

Steckverbinder A	1 - DVI-A (17-polig)
Steckverbinder B	1 - VGA (15-polig, High Density D-Sub)

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	28 AWG
Kabellänge	6.0 ft [1.8 m]
Produktlänge	6.0 ft [1.8 m]
Produktbreite	1.6 in [4.1 cm]
Produkthöhe	0.6 in [1.5 cm]
Produktgewicht	6.6 oz [186.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.4 in [18.7 cm]
Paketbreite	7.8 in [19.7 cm]
Pakethöhe	1.1 in [2.9 cm]
Versandgewicht (Verpackung)	6.8 oz [192.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 6 ft DVI to Coax High Resolution VGA Monitor Cable
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.