

6 ft DVI to Coax High Resolution VGA Monitor Cable

Productcode: DVIVGAMM6



The DVIVGAMM6 6-foot DVI to VGA Monitor Cable features a DVI (analog) male connector and a VGA (High Density D-Sub) male connector, providing a cost-effective way to connect an analog or a dual mode Flat Panel Display to a PC or Mac® computer with a DVI Analog Video Card.

Expertly designed and constructed of only high quality materials, the 6ft DVI to VGA Monitor cable is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Connects PC/Mac® with DVI Analog Video Card to an Analog or Dual-Mode Flat Panel Display

Eigenschappen

- Manufactured according to DVI specifications
- Molded connector ends with strain relief

Hardware

Garantiebeleid	Lifetime
Active or Passive Adapter	Passief
Connectormateriaal	Nikkel
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

Connector(en)

Connector A	1 - DVI-A (17-polig)
Connector B	1 - VGA (15-polig, D-Sub met hoge dichtheid)

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	6.0 ft [1.8 m]
Lengte product	6.0 ft [1.8 m]
Breedte product	1.6 in [4.1 cm]
Hoogte product	0.6 in [1.5 cm]
Gewicht product	6.6 oz [186.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	7.4 in [18.7 cm]
Package Width	7.8 in [19.7 cm]
Package Height	1.1 in [2.9 cm]
Verzendgewicht (verpakt)	6.8 oz [192.0 g]

Wat wordt er

meegeleverd

Meegeleverd

1 - 6 ft DVI to Coax High Resolution VGA Monitor Cable

Garantiebepalinge
n

Warranty

Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.