

## 2 Port 1b 1a ExpressCard 34mm Laptop 1394 FireWire Adapter Card

Produkt ID: EC13941A1B



This ExpressCard (34mm) dual port 1394 FireWire Adapter Card features two 1394 Firewire ports (1b, 1a) - adding both FireWire 400 and FireWire 800 connectivity to a laptop computer, with support for virtually any IEEE1394 device - a cost-effective and convenient solution for connecting FireWire devices to your laptop computer.

A convenient video editing solution, the ExpressCard FireWire adapter makes it easy to connect DV camcorders, external hard drives or FireWire audio/video devices to a laptop computer.

Plus, the Adapter card includes Ulead's Video Studio 10 software - ideal for editing video from FireWire devices through a notebook computer.

### Certifikat, rapporter och kompatibilitet



### Användning

- Add a high-speed FireWire port to a laptop without any FireWire ports
- Connect a digital camera to a laptop with an ExpressCard slot to download photos and video

- Connect a high-speed external hard drive to an ExpressCard-enabled system

## Funktioner

- One 9-pin FireWire 800 port with transfer rates up to 800Mbps
- One 6-pin FireWire 400 port with transfer rates up to 400Mbps
- Compliant with IEEE 1394b and backward compatible with IEEE 1394a - 2000 as well as 1394-1995 standards
- Optional external power support for high-powered FireWire devices
- Fits in both 34mm and 54mm ExpressCard slots
- Plug-and-Play and hot-swap compatible

---

### Hårdvara

|               |                      |
|---------------|----------------------|
| Garantipolicy | Lifetime             |
| Portar        | 2                    |
| Gränssnitt    | FireWire 400 (1394a) |
|               | FireWire 400 (1394a) |
| Busstyp       | ExpressCard          |
| Korttyp       | ExpressCard 34mm     |
| Chipset-ID    | LSI - FW643          |

---

### Prestanda

|                                  |                       |
|----------------------------------|-----------------------|
| Maximal dataöverföringshastighet | 1394A - Up to 400Mbps |
|                                  | 1394B - Up to 800Mbps |

---

### Kontakt(er)

|                |                                         |
|----------------|-----------------------------------------|
| Kontakttyp(er) | 1 - ExpressCard (34mm)                  |
| Externa portar | 1 - FireWire 400 (6-stifts, IEEE 1394a) |
|                | 1 - FireWire 800 (9-stifts, IEEE 1394b) |

---

## Mjukvara

|                   |                                                                                                                                                                    |
|-------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| OS-kompatibilitet | Windows 2000/ XP (32/64-bit)/ Server 2003 (32/64-bit)/ Server 2008 R2/ Vista (32/64-bit)/ 7 (32/64-bit)/ 8 (32/64-bit), Mac OS 10.4/ 10.5/ 10.6/ 10.7/ 10.8, Linux |
|-------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Särskilda anmärkningar/krav

|      |                                                                                      |
|------|--------------------------------------------------------------------------------------|
| Obs. | Optional power adapter specifications: 12VDC, 2000+ mA, Center positive, Type H plug |
|------|--------------------------------------------------------------------------------------|

## Ström

|            |                                                |
|------------|------------------------------------------------|
| Strömkälla | Medföljer ej (behövs ej vid vanlig användning) |
|------------|------------------------------------------------|

## Utseende

|              |                  |
|--------------|------------------|
| Produktlängd | 4.5 in [11.5 cm] |
| Produktbredd | 1.7 in [4.4 cm]  |
| Produkthöjd  | 0.8 in [2 cm]    |
| Produktvikt  | 1.1 oz [31 g]    |

## Förpackning

|                         |                  |
|-------------------------|------------------|
| Paketets längd          | 9.3 in [23.5 cm] |
| Paketets bredd          | 5.7 in [14.5 cm] |
| Paketets höjd           | 2.4 in [60 mm]   |
| Fraktvikt (förpackning) | 6.3 oz [178 g]   |

## Vad det är i lådan

|                 |                               |
|-----------------|-------------------------------|
| Ingår i paketet | 1 - ExpressCard FireWire Card |
|                 | 1 - FireWire Cable            |
|                 | 1 - Software CD               |
|                 | 1 - Instruction Manual        |

## Warranty Information

|          |           |
|----------|-----------|
| Warranty | Livslängd |
|----------|-----------|

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.