

## 2 Port ExpressCard 1394a FireWire Laptop Adapter Card

**Product ID:** EC13942A2



The EC13942A2 (2 Port) ExpressCard Laptop 1394a Firewire Adapter Card provides a stable platform for virtually any FireWire 400 device connection.

Ensuring seamless operation with peripherals connected through FireWire 400, the ExpressCard 1394a FireWire Adapter supports data transfer rates at up to 400Mbps - an ideal solution for connecting FireWire-capable multimedia devices, editing multimedia content or simply transferring large volumes of data from a computer to FireWire-connected external storage.

As an added convenience, the 2-port FireWire card is packaged with a FireWire cable.

This 2 port ExpressCard IEEE 1394a FireWire 400 Laptop adapter card is designed to fit a 34mm ExpressCard slot and is backed by a StarTech.com lifetime warranty.

## Certifications, Reports and Compatibility

### Applications

- Add a high-speed FireWire port to a laptop without any FireWire ports
- Connect a digital camera to a laptop with an ExpressCard slot to download photos and video
- Connect a high-speed external hard drive to an ExpressCard-enabled system

### Features

- Two external FireWire400 ports with support for transfer rates up to 400 Mbps

- 34mm ExpressCard/34 form factor
- Optional external power support for high-powered FireWire devices
- Complaint with IEEE 1394-1995, 2000, OHCI 1.1 standards
- Compliant with ExpressCard revision 1.0 standards
- Plug-and-Play and Hot-Swap compatible

---

#### Hardware

Warranty	Lifetime
Ports	2
Interface	FireWire 400 (1394a)
Bus Type	ExpressCard
Card Type	34mm ExpressCard
Chipset ID	VIA/VLI - VT6315

---

#### Performance

Type and Rate	FireWire 400 IEEE-1394a - 400 Mbit/s
---------------	--------------------------------------

---

#### Connector(s)

Connector Type(s)	ExpressCard (34mm)
External Ports	FireWire 400 (6 pin, IEEE 1394a)

---

#### Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2003, 2008 R2 Mac OS 10.6 to 10.11, Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
------------------	--

---

#### Power

Power Source	Not Included (not required for standard applications)
Output Voltage	12V DC
Output Current	1A
Center Tip Polarity	Positive



Plug Type	H
-----------	---

---

**Environmental**

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5~85% RH

---

**Physical Characteristics**

Product Length	4.5 in [11.5 cm]
Product Width	1.6 in [40 mm]
Product Height	0.6 in [14 mm]
Weight of Product	1.0 oz [29 g]

---

**Packaging Information**

Package Length	5.7 in [14.4 cm]
Package Width	6.7 in [17 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	4.1 oz [117 g]

---

**What's in the Box**

Included in Package	2 Port FireWire ExpressCard Adapter
	Firewire Cable
	Instruction Manual

---

*\*Product appearance and specifications are subject to change without notice.*

