

## 1 Port ExpressCard RS232 Serial Adapter Card with 16950 UART

**Product ID:** EC1S950



This 1 Port Serial ExpressCard Adapter lets you add a serial port to your laptop or ExpressCard equipped desktop computer, using an available ExpressCard slot.

Featuring 128-byte FIFO communication, and a high performance 16C950 UART, the ExpressCard Serial Adapter card offers up to 921.6Kbps data transfer rates, which ensures peak communication with your serial peripheral devices.

Designed to provide a durable serial connectivity solution, the Serial ExpressCard is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

### Certifications, Reports and Compatibility

### Applications

- Works with serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters, and more.

### Features

- Offers 1 DB9 RS-232 port to connect a serial device to a notebook PC
- 128-byte deep FIFO data buffer
- High Performance 16C950 UART with maximum data transfer rate up to 921.6 kbps
- Automated in-band flow control

---

**Hardware**

Warranty	Lifetime
Ports	1
Bus Type	ExpressCard
Card Type	34mm ExpressCard
Port Style	Integrated on Card
Chipset ID	PLX/Oxford - OXCB950

---

**Performance**

Maximum Data Transfer Rate	921000000 Mbits/Sec
Serial Protocol	RS-232

---

**Connector(s)**

Connector Type(s)	ExpressCard (34mm)
External Ports	DB-9 (9 pin, D-Sub)

---

**Software**

OS Compatibility	Windows 95/ 98SE/ ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Linux Kernel 2.6.11 and above,
------------------	--

---

**Special Notes / Requirements**

System and Cable Requirements	A notebook computer with an available ExpressCard slot (34mm or 54mm).
-------------------------------	--

---

**Packaging Information**

Package Length	9.0 in [22.8 cm]
Package Width	1.7 in [42 mm]
Package Height	6.3 in [16 cm]
Shipping (Package) Weight	7.1 oz [200.0 g]

---

**What's in the Box**

Included in Package	Serial ExpressCard  1 Port DB9 Break-out Cable
---------------------	--



Driver CD

Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

