2 Port Flush Mount ExpressCard 54mm eSATA II Controller Adapter Card

Produkt ID: ECESATA254F

The ECESATA254F Flush Mount 2-Port eSATA ExpressCard Adapter uses a unique slim 54mm form factor design that allows it to sit fully in a standard laptop ExpressCard/54 slot without sticking out. When installed, the ports sit flush with the sides of the laptop, creating a seamless add-on that can be left installed at all times, without fear that it or the card slot will be damaged due to snagging or impact.

The eSATA ExpressCard adapter features 2 independent eSATA ports, and is compatible with the latest high capacity SATA drives (SATA I, SATA II) with support for data transfer speeds up to 3 Gbps.

With support for Port Multiplier technology and hot-swap installation, the eSATA ExpressCard allows compatible multi-drive enclosures to be connected over a single eSATA cable, and devices can be connected and disconnected without having to reboot the system.

Certifikat, rapporter och kompatibilitet

RoHS Compliant | TAA COMPLIANT | CE | Windows 8 | Windows 7 | Windows Server 2012 | Linux

Användning

• Add high speed eSATA connectivity to a laptop that lacks built-in eSATA ports

• Connect eSATA peripherals such as external hard drives and optical drives, at native SATA speeds

Funktioner

• Unique, flush-mount slim ExpressCard/54 (54mm) form factor design

• Two independent eSATA channels

• Fully compatible with SATA revision (SATA 150, SATA 300) hard drives (HDD), solid state drives (SSD) and optical drives

• Support for FIS-based Port Multiplier

• Support for large capacity SATA drives through a 48-bit LBA

• Support for Legacy Command Queuing (LCQ) and Native Command Queuing (NCQ)

• PCI Express revision 1.0a compliant

• Plug-and-Play and hot-swap compatible

Hårdvara		
	Garantipolicy	2 Years
	Portar	2
	Gränssnitt	eSATA
	Busstyp	ExpressCard
	Korttyp	ExpressCard 54mm
	Chipset-ID	Silicon Image - SiI3132
Prestanda		
	Maximal dataöverföringshastighet	3.0 Gbps
	Typ och hastighet	SATA 3 Gbit/s (SATA II)
	Port Multiplier	Ja
	RAID	Nej

Kontakt(er)		
	Kontakttyp(er)	1 - ExpressCard (54mm)
	Externa portar	2 - eSATA (7-stifts, data)
Mjukvara		
	OS-kompatibilitet	Windows® 2000, XP, Vista, 7, 8, 8.1, 10
		Windows Server® 2003, 2008 R2, 2012
		Mac OS X® 10.6 to 10.11
		Linux 3.5.x to 4.4.x LTS Versions only
Särskilda anmärkningar/krav		
	System- och kabelkrav	ExpressCard/54 slot
Ström		
	Power Source	Medföljer ej (behövs ej vid vanlig användning)
Miljö		
	Drifttemperatur	0°C to 70°C (32°F to 158°F)
	Förvaringstemperatur	-65°C to 150°C (-85°F to 302°F)
Utseende		
	Färg	Svart & silver
	Produktlängd	3.0 in [7.5 cm]
	Produktbredd	2.1 in [5.4 cm]
	Produkthöjd	0.2 in [0.5 cm]
	Produktvikt	0.8 oz [22.5 g]
Förpackning		
	Förpackningsantal	1
	Package Length	6.9 in [17.5 cm]
	Package Width	5.7 in [14.5 cm]
	Package Height	1.2 in [3.0 cm]

	Fraktvikt (förpackning)	3.1 oz [88.0 g]

Vad det är i lådan

Ingår i paketet	1 - eSATA ExpressCard
	1 - Driver CD
	1 - Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.