

2 Port ExpressCard SuperSpeed USB 3.0 Card Adapter with UASP Support

Product ID: ECUSB3S22



The ECUSB3S22 2-Port ExpressCard USB 3.0 Card adds 2 SuperSpeed USB 3.0 ports to an ExpressCard-enabled computer system, using a 34mm form factor that will fit in both 34mm and 54mm slots, along with ports mounted side-by-side for easy access.

Enhanced with UASP support (USB Attached SCSI Protocol), this USB 3.0 controller performs up to 70% faster than conventional USB 3.0 when paired with a [%group id="114" text="UASP supported enclosure" append_qs="filter_UASP_YN=Yes"%] (Note: UASP requires a compatible operating system). Using a more efficient protocol than the traditional USB BOT (Bulk-Only Transport), UASP technology optimizes transfers by allowing multiple commands to be processed simultaneously, significantly increasing transfer speeds for less wait time on data transfers. See our UASP test results below for further details.

USB 3.0 supports data transfer rates up to 5 Gbps (10x faster than USB 2.0) and is able to provide more power per port, to help support faster and more powerful devices. Also, this ExpressCard adapter is backward compatible with USB 2.0/1.x, so all of your existing devices will still work.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

UASP is supported in Windows 8 and Server 2012. In testing UASP performed with up to a 70% faster read / 40% faster write speed over traditional USB 3.0 at peak performance.

At the same peak in testing, UASP also showed up to an 80% reduction in required processor resources.

Test results were obtained using an Intel Ivy Bridge system, StarTech.com add-on USB 3.0 cards, a UASP-enabled StarTech.com enclosure, and a SATA III solid state drive.

Certifications, Reports and Compatibility



Applications

- Laptop users looking to extend the life of their older mobile computers by adding USB 3.0 connectivity
- Expand on your laptop expansion capabilities with additional USB ports
- Professionals or home users looking to expand a laptops storage capabilities with high performance USB 3.0 external storage devices for large videos/images/etc.
- IT professionals looking to backup or archive large amounts of data off of a laptop quickly

Features

- Two SuperSpeed USB 3.0 compliant ports, with support for transfer rates up to 5 Gbps
- Built-in external DC power connector (optional)
- Compliant with USB 3.0 base specification 1.0 and xHCI specification 0.96
- Backward compatible with USB 2.0/1.x devices
- Compliant with PCI Express specification 2.0
- Side-by-side port mount design
- UASP support for more efficient data transfer

| | | |
|---------------------|-------------------------------------|---|
| Hardware | Warranty | Lifetime |
| | Ports | 2 |
| | Interface | USB 3.0 |
| | Bus Type | ExpressCard |
| | Card Type | 34mm ExpressCard |
| | Chipset ID | Renesas/NEC - PD720200 |
| Performance | Maximum Data Transfer Rate | 5 Gbps USB 3.0 - 5 Gbit/s |
| | Type and Rate | Yes |
| | UASP Support | |
| Connector(s) | Connector Type(s) | ExpressCard (34mm) |
| | External Ports | USB Type-A (9 pin) USB 3.0 (5 Gbps) |
| Software | OS Compatibility | Windows 10 (32/64), 8 / 8.1 (32/64), 7 (32/64), Vista (32/64), XP (32/64) Windows Server 2008 R2, 2003 |
| | Special Notes / Requirements | Note Due to the power limitations of the ExpressCard interface this adapter cannot supply 900mA of current to both ports. Some devices like External 2.5" Hard Drives may require an additional power adapter. The maximum throughput of this card is limited by the host bus interface. If used with ExpressCard Gen 1.0 enabled computers, the max throughput is 2.5 Gbps. If used with ExpressCard Gen 2.0 |

enabled computers, the max throughput is 5 Gbps

| | | |
|---------------------------------|---------------------------|---|
| Power | Power Source | Not Included (not required for standard applications) |
| | Output Voltage | 5 DC |
| | Plug Type | B |
| Environmental | Operating Temperature | 0C to 50C (32F to 122F) |
| | Storage Temperature | -20C to 150C (-4F to 302F) |
| | Humidity | 0% ~ 60% RH |
| Physical Characteristics | Material | Steel |
| | Product Length | 4.5 in [1.2 cm] |
| | Product Width | 1.6 in [40 mm] |
| | Product Height | 0.5 in [12 mm] |
| | Weight of Product | 1.1 oz [32 g] |
| Packaging Information | Package Quantity | 1 |
| | Package Length | 5.7 in [1.4 cm] |
| | Package Width | 6.8 in [1.7 cm] |
| | Package Height | 1.3 in [32 mm] |
| | Shipping (Package) Weight | 4.2 oz [119 g] |
| What's in the Box | Included in Package | ExpressCard USB 3.0 Card |
| | Included in Package | Driver CD |
| | Included in Package | USB to DC Power Cable |
| | Included in Package | Instruction Manual |

****Product appearance and specifications are subject to change without notice.***

