

Easel-Style TV Cart for up to 100-inch and 220lb / 100kg Displays, Height Adjustable Rolling / Mobile Stand, 3" Lockable Wheels for Easy Transport

Product ID: ELB1-TV-CART



This easel-style TV cart is designed to reposition large-format screens effortlessly between rooms while maintaining a minimal look that fits into professional or educational environments. Support displays up to 100-inch and 220lb (100kg).

The display height can be adjusted during assembly positioning the center of the screen between 49.1 and 56.2in (1.25 to 1.43 m) from the floor. This helps position the display size or interactive whiteboard to the ideal viewing height for your room layout and audience size.

The easel style design positions the legs higher on the frame and keeps them within clear view, helping reduce tripping hazards in high-traffic areas where students or presenters walk past the cart. Large, smooth-rolling and lockable 3in (7.5cm) wheels provide controlled movement through standard doorways, hallways, elevators, and other shared areas, making it easy to relocate and secure the display wherever it's needed.

Broad compatibility ensures the mobile cart works with a wide range of smart whiteboards, commercial TVs, and digital signage, thanks to support for VESA patterns from 300x300 to 1000x600 mm. The steel construction and smooth powder-coated finish offer long-lasting durability and provide an easy-to-clean surface after daily use.

For added convenience, an integrated 7.5 in. (19 cm) shelf creates an area under the screen to keep essential accessories such as a laptop, pens, laser pointers, or other tools within reach during lessons, presentations, or interactive sessions.

Certifications, Reports and Compatibility

Applications

Features

- **Streamline Mobility for Large-Format Displays**: Modern easel-style movable TV cart safely and smoothly moves screens up to 100-inch and 220lb (100kg) between boardrooms and classrooms while keeping a sleek and minimalistic aesthetic
- **Adjustable Height**: Set the height of the interactive board or display based on the screen size or the audience's viewing needs, using the three height positions from 49.1 to 56.2in (1.25 to 1.43m) measured from the floor to the center of the TV
- **Safer Spaces and Easy Mobility**: Easel-style frame clearly stands out from all angles, minimizing tripping hazards in high-traffic areas; Smooth-rolling and lockable 3in (7.5cm) wheels provide controlled movement through standard doors, hallways, elevators
- **Display Compatibility and Durability**: Supports VESA up to 1000x600mm, making it a versatile fit for smart whiteboards, commercial TVs, and digital signage, while its steel construction and powder-coated finish withstand daily use and clean easily
- **Keep Essential Accessories Within Reach**: Mobile TV stand features an integrated 7.5in (19cm) wide shelf providing a convenient spot for a laptop, pens, laser pointers, or other small accessories used in classrooms and boardroom setups

Hardware

Warranty	5 Years
Casters	Included
# of Displays Supported	1
Orientation	Horizontal
Mounting Options	Mobile Cart
VESA Hole Pattern(s)	300x300 mm
	400x400 mm
	600x400 mm
	800x400 mm
	800x600 mm
	1000x600 mm

Performance

Weight Capacity (Per Display)	0.2 lb [0.1 kg]
Minimum Display Size	65"

Maximum Display Size	100"
Fits Curved Display	No
Video Wall	No
Height Adjustment	Yes
Minimum Height	49.2 in [125 cm]
Maximum Height	56.3 in [143 cm]
Anti-theft	No

Physical Characteristics

Color	Space Gray
Construction Material	Steel and Plastic
Product Length	46.1 in [1170 mm]
Product Width	30.6 in [778 mm]
Product Height	68.4 in [1738 mm]
Weight of Product	784.6 oz [22226 g]

Packaging Information

Package Length	33.7 in [85.5 cm]
Package Width	4.0 ft [1.2 m]
Package Height	7.3 in [18.5 cm]
Shipping (Package) Weight	66.2 lb [30.0 kg]

What's in the Box

Included in Package	1 - Column, Left
	1 - Column, Right
	1 - Lower Frame, Left
	1 - Lower Frame, Right

- 1 - Shelf
- 1 - TV Mounting Bracket
- 4 - Casters
- 2 - TV VESA Brackets
- 4 - Spring Washers
- 4 - 16mm Ø Washers
- 4 - 12.5mm Ø Washers
- 4 - M6x16mm Screws
- 16 - M8x20mm Screws
- 4 - M8x25mm Screws
- 1 - Quick-Start Guide

**Warranty
Information**

Warranty

5 Years

****Product appearance and specifications are subject to change without notice.***