

2m Shielded External eSATA Cable M/M

Product ID: ESATA2M



The ESATA2M 2m Shielded eSATA cable provides a high quality connection between your desktop or laptop computer and an external SATA storage device, and is compliant with SATA III specifications, supporting data transfer rates of up to 6 Gbps.

Designed for optimum performance and reliability, this 2m eSATA cable is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to an external SATA storage device (e.g. external eSATA hard drive)

Features

- 2x eSATA connectors
- Supports full SATA 3.0 6Gbps bandwidth

Hardware

Warranty

Lifetime

	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
<hr/>		
Connector(s)		
	Connector A	1 - eSATA (7 pin, Data)
	Connector B	1 - eSATA (7 pin, Data)
<hr/>		
Physical Characteristics		
	Color	Black
	Wire Gauge	26 AWG (0.404 mm)
	Cable Length	6.6 ft [2 m]
	Product Length	6.6 ft [2.0 m]
	Product Width	0.0 in [0.0 cm]
	Product Height	0.0 in [0.0 cm]
	Weight of Product	4.7 oz [132.0 g]
<hr/>		
Packaging Information		
	Package Quantity	1
	Package Length	8.8 in [22.3 cm]
	Package Width	4.8 in [12.2 cm]
	Package Height	0.4 in [1.0 cm]
	Shipping (Package) Weight	4.8 oz [135.0 g]
<hr/>		
What's in the Box		
	Included in Package	1 - 2m Shielded External eSATA Cable M/M
<hr/>		

****Product appearance and specifications are subject to change without notice.***