

## 2m Shielded External eSATA Cable M/M

**Product ID:** ESATA2M



The ESATA2M 2m Shielded eSATA cable provides a high quality connection between your desktop or laptop computer and an external SATA storage device, and is compliant with SATA III specifications, supporting data transfer rates of up to 6 Gbps.

Designed for optimum performance and reliability, this 2m eSATA cable is backed by our lifetime warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your desktop or laptop computer to an external SATA storage device (e.g. external eSATA hard drive)

### Features

- 2x eSATA connectors
- Supports full SATA 3.0 6Gbps bandwidth

---

#### Hardware

Warranty

Lifetime

Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A	1 - eSATA (7 pin, Data)
Connector B	1 - eSATA (7 pin, Data)

---

**Physical Characteristics**

Color	Black
Wire Gauge	26 AWG (0.404 mm)
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	4.7 oz [132.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.8 in [22.3 cm]
Package Width	4.8 in [12.2 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	4.8 oz [135.0 g]

---

**What's in the Box**

Included in Package	1 - 2m Shielded External eSATA Cable M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***