

2m Shielded External eSATA Cable M/M

Product ID: ESATA2M



The ESATA2M 2m Shielded eSATA cable provides a high quality connection between your desktop or laptop computer and an external SATA storage device, and is compliant with SATA III specifications, supporting data transfer rates of up to 6 Gbps.

Designed for optimum performance and reliability, this 2m eSATA cable is backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to an external SATA storage device (e.g. external eSATA hard drive)

Features

- 2x eSATA connectors
- Supports full SATA 3.0 6Gbps bandwidth

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	eSATA (7 pin, Data)
Connector B	eSATA (7 pin, Data)

Physical Characteristics

Color	Black
Wire Gauge	26 AWG (0.404 mm)
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2 m]
Weight of Product	4.7 oz [132 g]

Packaging Information

Package Quantity	1
Package Length	8.8 in [22.3 cm]
Package Width	4.8 in [12.2 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	4.8 oz [135 g]

What's in the Box

Included in Package	2m Shielded External eSATA Cable M/M
---------------------	--------------------------------------

****Product appearance and specifications are subject to change without notice.***

