


## 1 ft eSATA Panel Mount Cable - F/M

**Product ID:** ESATAPNLFM1



The ESATAPNLFM1 1-foot eSATA Panel Mount Cable provides a well-secured, easy-to-access eSATA connection on any device port or faceplate.

Constructed of only high quality materials and expertly designed for reliability and peak performance, the ESATAPNLFM1 cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Provides an eSATA panel mount connection from your SATA controller

### Features

- A panel mount eSATA port with screws to allow for secure installation
- Support fast data transfer rates of up to 6 Gbps
- Compliant with Serial ATA III Specifications

---

#### Hardware

Warranty	Lifetime
Cable Jacket Material	PVC

---

**Performance**

Type and Rate                      SATA III (6 Gbps)

---

**Connector(s)**

Connector A                          SATA (7 pin, Data)

Connector B                          eSATA (7 pin, Data)

---

**Environmental**

Operating Temperature            0C to 50C (32F to 122F)

Storage Temperature            -20C to 70C (-4F to 158F)

Humidity                              0% to 90% RH

---

**Physical Characteristics**

Color                                  Red

Wire Gauge                          26 AWG (0.404 mm)

Cable Length                      12.0 in [30.5 cm]

Weight of Product                 0.8 oz [24 g]

---

**Packaging Information**

Package Quantity                  1

Package Length                    4.9 in [12.5 cm]

Package Width                     8.9 in [22.5 cm]

Package Height                    0.4 in [10 mm]

Shipping (Package) Weight      0.9 oz [26 g]

---

**What's in the Box**

Included in Package              1 ft eSATA Panel Mount Cable - F/M

---

*\*Product appearance and specifications are subject to change without notice.*

