

3 ft eSATA and USB A to Power eSATA Cable - M/M

Product ID: ESATAUSBMM3



This eSATA and USB A Male to Power eSATA Cable provides a 3ft connection between an external drive enclosure equipped with a power eSATA port and the eSATA and USB port on a PC/Notebook, providing both power (through USB) and data (through SATA) using a single cable.

Expertly designed and constructed of only top quality materials, the 3ft eSATA and USB A Male to Power eSATA Male cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your Powered eSATA device to your PC or Notebook even if you do not have a Powered eSATA port

Features

- 1x eSATA 11-pin Power receptacle
- 1x eSATA 7-pin Data receptacle
- 1x USB-A male connector
- Supports full SATA 3.0 6Gbps bandwidth

Hardware

Warranty

Lifetime

Cable Jacket Material	PVC - Polyvinyl Chloride
-----------------------	--------------------------

Connector(s)

Connector A	Power eSATA (11 pin, eSATA/USB, 5/12V)
Connector B	eSATA (7 pin, Data)
	USB Type-A (4 pin) USB 2.0

Environmental

Operating Temperature	-20C to 50C (-4F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	60~75% RH

Physical Characteristics

Color	Black
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Weight of Product	3.0 oz [84.6 g]

Packaging Information

Package Length	4.6 in [11.8 cm]
Package Width	0.7 in [19 mm]
Package Height	8.5 in [21.6 cm]
Shipping (Package) Weight	3.1 oz [87.3 g]

What's in the Box

Included in Package	3ft USB and ESATA to Power eSATA
---------------------	----------------------------------

**Product appearance and specifications are subject to change without notice.*

