

10/100 Mbps Multi Mode Fiber Media Converter ST 2 km

Produkt ID: ET90110ST2



The ET90110ST2 10/100 Mbps Multimode Fiber Media Converter (ST, 2 km) lets you extend a Fast Ethernet network (10/100 Mbps) over multimode fiber, at distances of up to 2 km (1.2 miles).

A cost-effective solution for connecting a 10/100 Mbps Ethernet (10/100Base-T) network to remote network segments over a 100Base-FX fiber backbone. Designed to offer a durable and convenient Ethernet to fiber solution, the Ethernet to ST Fiber converter features an all-steel chassis, and a simple plug-and-play installation with minimal configuration required.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Provides connectivity to a user or network segment that is in an isolated area of a large complex or in another building altogether
- Perfect for secure connections required by government agencies where EMI is not acceptable
- Connect traffic control/monitoring systems at extreme distances to the main office
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues
- Converts 100Base-FX fiber optic signals to 10/100Base-T Ethernet over multi mode fiber cable

Funktioner

- Cost-effective way to extend/bridge networks using fiber cabling
- Advanced features include Link-loss forwarding, remote monitor status, two frame lengths
- Supports a maximum fiber cable length of 2 km
- Supports full or half-duplex operation
- Quick and simple installation, easy to use

Hårdvara

Garantipolicy	2 Years
PoE	Nej
WDM	Nej

Prestanda

Maximal dataöverföringshastighet	200 Mbps (Full Duplex Mode)
Maximalt överföringsavstånd	2 km (1.2 mi)
Fibertyp	Multiläge
Våglängd	1310nm
Fiber-driftsläge	Halv/full-duplex
Auto MDIX	Ja

Kontakt(er)

Lokala enhetskontakter	RJ-45
Fjärrenhetskontakter	Fiberoptisk ST duplex

Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.48 A



Utspänning	12V DC
Utström	1.6 A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	19.2

Miljö

Drifttemperatur	0°C to 60°C (32°F to 140°F)
Förvaringstemperatur	-10°C to 70°C (14°F to 158°F)
Luftfuktighet	10~90% RH

Utseende

Färg	Svart
Kabinetttyp	Stål
Produktlängd	6.1 in [15.4 cm]
Produktbredd	3.4 in [87 mm]
Produkthöjd	0.9 in [24 mm]
Produktvikt	13.7 oz [387 g]

Förpackning

Package Length	5.4 in [13.7 cm]
Package Width	8.1 in [20.7 cm]
Package Height	3.5 in [90 mm]
Fraktvikt (förpackning)	26.7 oz [757 g]

Vad det är i lådan

Ingår i paketet	Fiber Media Converter
	Universal Power Adapter (NA/EU/UK/AU)
	Grounding Screw



Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

