

Citrix EW3Z0000587 Compatible SFP Module - 1000BASE-LX - 1GbE Single Mode Fiber SMF Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 10km - 1310nm - DDM

Product ID: EW3Z0000587-ST



The EW3Z0000587-ST is a Citrix EW3Z0000587 compatible fiber transceiver module that has been designed, programmed and tested to work with Citrix brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000Base-LX compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1310nm
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 634,210,013 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **100% CITRIX EW3Z0000587 COMPATIBLE SFP TRANSCEIVER:** Designed, programmed and tested to work with compatible Citrix switches and routers to deliver dependable 1GbE connectivity
- **TECHNICAL SPECS:** 1000BASE-LX 1Gbps Single Mode (SMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Citrix routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	Citrix
Industry Standards	IEEE 802.3z 1000BASE-LX

Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1310nm
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	634,210,013 hours
Power Consumption (In	< 1.3W

Watts)

**Physical
Characteristics**

Product Length	0.5 in [13.7 mm]
Product Width	2.2 in [56.6 mm]
Product Height	0.5 in [12.5 mm]
Weight of Product	0.6 oz [18 g]

**Packaging
Information**

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90 mm]
Package Height	1.2 in [31 mm]
Shipping (Package) Weight	1.8 oz [50 g]

**What's in the
Box**

Included in Package	SFP Transceiver
---------------------	-----------------

****Product appearance and specifications are subject to change without notice.***

