

Juniper EX-SFP-1GE-T Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m

Product ID: EXSFP1GETST



The EXSFP1GETST is a Juniper EX-SFP-1GE-T compatible copper transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over copper cable, for 10BASEBASE-T, 100BASE-TX and 1000BASE-T compliant networks, with a maximum distance of up to 100 m (328 ft.).

 1000 Mbps Copper RJ45 Connector 100 m (328 ft.) 4,655,371 hours Less than 1.3 Watts No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP modules in Juniper switches and routers
- Expand your network to remote segments

Features

- **100% JUNIPER EX-SFP-1GE-T COMPATIBLE SFP TRANSCEIVER:** Designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- **TECHNICAL SPECS:** 1000BASE-T 1Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Juniper routers and switches
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware	Warranty	Lifetime
	Compatible Brand	Juniper
	Industry Standards	IEEE 802.3i 10BASE-T
	Industry Standards	IEEE 802.3ab 1000BASE-T
	Industry Standards	IEEE 802.3u 100BASE-TX
Performance	Maximum Data Transfer Rate	1000 Mbps
	Max Transfer Distance	100 m (328 ft)
	Type	Copper
	Fiber Operating Mode	Full-Duplex
	DDM	No
	Compatible Networks	10/100/1000 Mbps
	MTBF	4,655,371 hours
	Power Consumption (In Watts)	< 1.3 W
Connector(s)	Local Unit Connectors	RJ-45
Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 85C (-40F to 185F)
	Humidity	5~95% RH
Physical Characteristics	Product Length	2.7 in [68.000 mm]
	Product Width	0.5 in [13.700 mm]
	Product Height	0.5 in [13.800 mm]
	Weight of Product	0.8 oz [24.000 g]
Packaging Information	Package Length	4.7 in [1.2 cm]

Package Width	3.7 in [94.000 mm]
Package Height	1.3 in [32.000 mm]
Shipping (Package) Weight	1.8 oz [51.000 g]

What's in the Box	Included in Package	SFP transceiver
--------------------------	---------------------	-----------------

****Product appearance and specifications are subject to change without notice.***

