

120x25mm Dual Ball Bearing Computer Case Fan w/ LP4 Connector

Product ID: FANBOX12



This versatile 12cm PC case fan is designed to fit a broad range of computer case designs, to circulate cool air into the case, or exhaust warm air out - preventing problems due to overheating components.

A quiet cooling solution, the 12cm dual ball-bearing case fan features a high efficiency blade design that's capable of moving 72.94 CFM throughout the computer case, helping to optimize system performance.

This broadly compatible PC cooling solution can be powered through a simple LP4 connection to the computer power supply, and is backed by StarTech.com's 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Replace a noisy or failed computer case fan
- Install into a computer to increase air flow and cooling

Features

- Inline LP4 power connectors
- Dual ball bearing design

Hardware

Warranty

2 Years

Number of Conductors 2

Fan Bearing Type Ball Bearing

Performance

Air Flow Rate 72.94 CFM

Noise Level 30 dBA

Fan RPM 2000

Connector(s)

Connector Type(s) LP4 (4 pin; Large Drive Power)

LP4 (4 pin; Large Drive Power)

Power

Input Voltage 12V DC

Environmental

Operating Temperature -10C to 80C

Physical Characteristics

Color Black

Material Plastic

Cable Length 12.0 in [30.5 cm]

Product Length 4.7 in [12.0 cm]

Product Width 1.0 in [25.0 mm]

Product Height 4.7 in [12.0 cm]

Weight of Product 4.4 oz [125.0 g]

Packaging Information

Package Length 8.0 in [20.3 cm]

Package Width 5.8 in [14.7 cm]

Package Height 1.2 in [30.0 mm]



Shipping (Package) Weight	6.2 oz [177.0 g]
------------------------------	------------------

**What's in the
Box**

Included in Package	12cm Case Fan
	Mounting Screws

****Product appearance and specifications are subject to change without notice.***

