

92x25mm Dual Ball Bearing Computer Case Fan w/ LP4 Connector

Produkt ID: FANBOX92



This 9.2cm x 9.2cm x 2.5cm (3 5/8" x 3 5/8" x 1") Dual Ball Bearing PC case fan is an add-in cooling fan designed to fit most computers.

The PC Case fan can be used to circulate cool air into the case or exhaust warm air out, preventing problems due to overheating components.

A quiet running brushless ball bearing DC motor coupled with a high efficiency blade design is capable of moving 39.35 CFM (cubic feet per minute) of air.

Power is supplied to the fan using a standard LP4 (hard drive power connector) pass through plug.

Certifikat, rapporter och kompatibilitet



Användning

- Replace a noisy or failed computer case fan
- Install into a computer case to increase air flow and cooling

Funktioner

- 92mm dual ball bearing fan design
- Inline LP4 power connectors

Hårdvara

Garantipolicy	2 Years
Antal ledare	2
Fläktlagerstyp	Kullager

Prestanda

Luftflödes hastighet	39.35 CFM
Bullernivå	26 dBA
Fläkt rpm	2200

Kontakt(er)

Kontakttyp(er)	1 - LP4 (4-stift, Molex-type Large Drive Power)
	1 - LP4 (4-stift, Molex-type Large Drive Power)

Ström

Inspänning	12V DC
------------	--------

Miljö

Drifttemperatur	-10°C to 80°C
-----------------	---------------

Utseende

Färg	Svart
Kabinetttyp	Av plast
Produktlängd	3.6 in [92 mm]
Produktbredd	1.0 in [2.5 cm]
Produkthöjd	3.6 in [9.2 cm]
Produktvikt	2.9 oz [82 g]

Förpackning

Förpackningsantal	1
-------------------	---

Paketets längd	5.6 in [14.2 cm]
Paketets bredd	3.8 in [9.7 cm]
Paketets höjd	1.3 in [3.3 cm]
Fraktvikt (förpackning)	4.0 oz [112.0 g]

Vad det är i lådan

Ingår i paketet	1 - 92mm Case Fan
	4 - Mounting Screws

Warranty
Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.