

USB 3.0 Multi Media Flash Memory Card Reader with 2-Port USB 3.0 Hub & USB Fast Charge Port

Product ID: FCREADU3HC



The FCREADU3HC USB 3.0 card reader lets you quickly mount all major media card types onto your desktop or laptop computer through a USB 3.0 port. The card reader supports the most common mass storage device formats, including CompactFlash, SecureDigital and MemoryStick cards, making it the perfect high-bandwidth solution for your photography and videography workstation.

Plus, the card reader is backward compatible with USB 2.0 and USB 1.1 computer systems, making it a great addition to any USB-enabled computer.

Plus, the card reader lets you keep your tablets and smartphones charged and ready to go, and saves you time with an integrated USB 2.0 fast charging port that charges your mobile devices such as Apple iPad & iPhone and Android devices, as quickly as if you were connected to a wall outlet. . This fast charge port has been specially designed for compatibility with a wide range of tablets and smartphones.

The card reader also lets you connect additional USB 3.0 devices to your computer through the same high-speed USB host connection, with a built-in 2-port USB 3.0 hub.

The FCREADU3HC USB 3.0 card reader is backed by a StarTech.com 2-year warranty, and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Access flash memory cards from your laptop
- Quickly transfer or edit photos and video from your memory cards to your computer, harnessing the speed of USB 3.0

- Sync your mobile device with your computer while charging faster than it would charge directly to your computer

Features

- Compatible with various types of CompactFlash, SecureDigital and MemoryStick flash cards
- USB fast charge port, charges mobile devices faster than a standard USB port
- Built-in 2-port USB 3.0 hub
- Compatible with USB 3.0/2.0/1.1 (5 Gbps / 480 Mbps / 1.5 Mbps)
- Universal power adapter included

Hardware

Warranty	2 Years
Bus Type	USB 3.0
Chipset ID	Genesys Logic - GL3520

Performance

Memory Media Type	MS Duo, MS Pro Duo, MS Pro-HG Duo CF (Compact Flash I Card) SDXC (Secure Digital eXtended Capacity) SDHC (Secure Digital High Capacity) microSDHC (Micro Secure Digital High Capacity) SD/MMC (Secure Digital/Multimedia Card) M2 (Memory Stick Micro) MS MG (Memory Stick w/ MagicGate) MS/MS Pro (Memory Stick/Memory Stick Pro) RS-MMC (Reduced Size Multimedia Card) MSXC (Memory Stick eXtended Capacity) Mini-SD, Micro-SD (Mini/Micro Secure Digital)
-------------------	---

Connector(s)

Connector Type(s)	USB Type-B (9 pin) USB 3.0
-------------------	----------------------------



External Ports	USB 3.0 A (Fast-Charge, 9 pin)
	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	SD / MMC Slot
	MicroSD
	CompactFlash (50 pin) Slot
	MiniSD / MicroSD / MMC Slot

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Indicators

LED Indicators	Power
----------------	-------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8 A
Output Voltage	5 DC
Output Current	4 A
Center Tip Polarity	Positive
Plug Type	C
Power Consumption (In Watts)	20

Environmental

Operating Temperature	-10C to 40C (14F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	90%

Physical Characteristics

Product Length	4.4 in [11.1 cm]
----------------	------------------



Product Width	2.4 in [60 mm]
Product Height	1.0 in [26 mm]
Weight of Product	3.8 oz [108 g]

Packaging Information

Package Length	6.2 in [15.8 cm]
Package Width	5.2 in [13.3 cm]
Package Height	2.8 in [70 mm]
Shipping (Package) Weight	16.4 oz [465 g]

What's in the Box

Included in Package	USB 3.0 Memory Card Reader
	USB 3.0 Cable
	Universal Power Adapter (NA/JP, UK, EU, ANZ)
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

