

VESA TV Wall Mount, Adjustable Full Motion Mount For 23"-55" Displays, Slim Wall Mount TV Bracket Supports 66lb (30kg), Extendable/Tilting/Swivel Monitor Wall Mount

**Product ID:** FHA-TV-WALL-MOUNT



The steel and aluminum construction of this VESA TV Wall Mount supports TVs from 23" to 55" and up to 66lb (30kg). The arm assembly provides smooth one-touch height adjustment thanks to its spring-loaded mechanism that acts as a counterbalance. The VESA plate supports mounting patterns of 75x75 to 400x400.

Securely mount a flat or curved-screen TV or digital signage in a convenient location for viewing by visitors, clients, and employees. This TV wall mount is ideal for lobbies, boardrooms, and manufacturing facilities. The lateral range of 3.54 ft (1.08m) is ideal for corner mounting. The jointed arm folds on itself and creates a slim profile from the wall of just 2.2in (5.8cm) for limited space installations. The minimum TV weight is 17.6lb (8kg). M5/M6/M8 Screws of various lengths and an assortment of washers and spacers enhance TV mounting compatibility. Mount into wood-stud or concrete walls, using the included hardware.

Supported VESA mounting patterns: 75x75, 100x100, 200x100, 200x200, 300x300, 400x200, and 400x400.

The VESA plate swivels +90 / -90 degrees, tilts +8 / -15 degrees, and rotates +3 / -3 degrees. Customize the viewing experience and comfort with these full-motion capabilities. The one-touch spring-assisted mechanism facilitates effortless height adjustments, with a range of up to 12.6in (32cm).

The arm assembly extends up to 23.4 in (59.5 cm) from the wall to accommodate different viewing positions.

The robust steel and aluminum design safely and securely supports the TV. The arm assembly features built-in cable management and a wall mount cover for an organized and visually appealing installation.

The height adjustable TV wall mount is backed for two years, including free lifetime 24/5 multi-lingual technical assistance.

## Certifications, Reports and Compatibility

## Applications

## Features

- **HEIGHT ADJUSTABLE TV WALL MOUNT:** Spring-assisted height adjustable range 12.6in (32cm); Articulating wall mount TV bracket supports TVs up to 55in; Max weight 66lb (30kg); Single-stud design made from powder-coated diecast aluminum for maximum durability
- **ONE-TOUCH MOTION:** Full-motion TV wall mount features a spring mechanism for effortless viewing angle and height adjustments; VESA plate features +/-90 swivel, +/-15 tilt, and +/-3 rotation; Toolless adjustment w/ built-in cable management
- **RANGE OF MOTION:** Low profile VESA TV wall mount with jointed arm assembly supports +/-90 swivel and folds to just 2.2in (5.8cm) from the wall; Max arm extension 23.4in (59.5cm); Lateral range of 3.9ft (1.19m) ideal for corner mounting maximizing space
- **COMPATIBILITY:** TV mounting bracket supports TVs up to 55" from LG, Samsung, Sony, Hisense, Sharp, and other TVs; Compatible VESA patterns: 75x75, 100x100, 200x100, 200x200, 300x300, 400x200, and 400x400; Spacers and various M5/M6/M8 screws included
- **QUICK AND CLEAN INSTALLATION:** Swivel TV wall mount ships pre-assembled for quick deployment; Wall plate with mounting holes facilitate simplified installation; Includes installation template, bubble level, wood studs, and concrete wall mounting hardware

---

### Hardware

Warranty	2 Years
Wallmountable	Yes
Cable Management	Yes
Tools Included	Yes
Articulating	Yes
# of Displays Supported	1
Orientation	Horizontal
Mounting Options	Wall-Mount
Minimum Profile from Wall	2.3 in [58 mm]
VESA Hole Pattern(s)	75x75 mm
	100x100 mm
	200x100 mm

200x200 mm

300x300 mm

400x200 mm

400x400 mm

---

**Performance**

General Specifications	Minimum Distance to Wall: 2.2 in (5.8 cm)
	Maximum Distance to Wall: 23.4 in (59.5 cm)
Weight Capacity (Per Display)	66.2 lb [30 kg]
Minimum Display Size	23"
Maximum Display Size	55"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Video Wall	No
Height Adjustment	Yes
Minimum Arm Extension	2.3 in [58 mm]
Maximum Arm Extension	21.4 in [544.2 mm]
Display Tilt	+8 / -15
Display Swivel	180
Display Rotation	+3 / -3
Anti-theft	No

---

**Physical Characteristics**

Color	Black & Silver
Construction Material	Aluminum and Steel
Product Length	23.4 in [59.5 cm]
Product Width	17.7 in [45.0 cm]

Product Height 17.7 in [45.0 cm]

Weight of Product 10.6 lb [4.8 kg]

---

**Packaging Information**

Package Quantity 1

Package Length 24.8 in [63.0 cm]

Package Width 19.5 in [49.5 cm]

Package Height 3.9 in [10.0 cm]

Shipping (Package) Weight 15.2 lb [6.9 kg]

---

**What's in the Box**

Included in Package

- 1 - Arm assembly
- 2 - Decorative covers
- 2 - VESA extension plates, LH
- 2 - VESA extension plates, RH
- 8 - VESA extension plate screws
- 1 - Wrench
- 1 - 4mm hex key
- 1 - 6mm hex key
- 1 - Bubble level
- 4 - M5x14mm screws
- 4 - M6x14mm screws
- 4 - M6x30mm screws
- 4 - M8x30mm screws
- 4 - M8x50mm screws
- 4 - Display washers, small
- 4 - Display washers, large

8 - Short spacers

8 - Tall spacers

5 - Wall mounting screws

5 - Concrete anchors

5 - Wall mounting washers

1 - Manual

---

***\*Product appearance and specifications are subject to change without notice.***