


7m Fiber Optic Cable - Multimode Duplex 62.5/125 LSZH Fiber Jumper Cord - LC/SC

Produkt-ID: FIBLCSC7



The FIBLCSC7 7-meter (23ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one LC (male) connector and one SC (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This LC-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our LC-SC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Used by long distance networks with mission critical data
- Telecommunication/Data communication

- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

Merkmale

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

Hardware

Garantiebestimmungen	Lifetime
Faseroptikgröße	62.5/125
Feuerwiderstandssklasse	LSZH-bewertet (Low Smoke Zero Halogen)
Faseroptikklassifizierung	OM1

Leistung

Max. Datenübertragungsrate	10 Gbit/s
Kabelnennwerte	1Gbps / 10Gbps
Faseroptiktyp	Multimodus

Steckverbinder

Steckverbinder A	1 - Faseroptik LC
Steckverbinder B	1 - Faseroptik SC

Umgebungsbedingungen

Betriebstemperatur	-20°C to 60°C (-4°F to 140°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)
Feuchtigkeit	0 bis 90 % relative Luftfeuchtigkeit

Physische
Eigenschaften

Farbe	Orange
Kabellänge	23.0 ft [7 m]
Produktlänge	23.0 ft [7.0 m]
Produktbreite	0.0 in [0.0 cm]
Produkthöhe	0.0 in [0.0 cm]
Produktgewicht	3.5 oz [99 g]

Verpackungsinform
ationen

Paketmenge	1
Paketlänge	6.7 in [16.9 cm]
Paketbreite	7.7 in [19.5 cm]
Pakethöhe	1.0 in [2.6 cm]
Versandgewicht (Verpackung)	4.0 oz [112.0 g]

Garantieinformatio
nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.