


Fiber Optic Cable - Multimode Duplex 62.5/125 - LSZH - LC/SC - 7 m

**Product ID:** FIBLCSC7



The FIBLCSC7 7-meter (23ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one LC (male) connector and one SC (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This LC-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our LC-SC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

## Certifications, Reports and Compatibility

### Applications

- Used by long distance networks with mission critical data
- Telecommunication/Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

## Features

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

---

### Hardware

Warranty	Lifetime
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Size	62.5/125

---

### Performance

Maximum Data Transfer Rate	10Gbps
Cable Rating	1Gbps / 10Gbps
Fiber Classification	OM1
Type	Multi Mode

---

### Connector(s)

Connector A	Fiber Optic LC Duplex
Connector B	Fiber Optic SC Duplex

---

### Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~90% RH

---

### Physical Characteristics

Color	Orange
Cable Length	23.0 ft [7 m]
Product Length	23.0 ft [7 m]

---

### Packaging Information



Package Length	7.8 in [19.9 cm]
Package Width	0.6 in [14 mm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	2.5 oz [70 g]

---

***\*Product appearance and specifications are subject to change without notice.***

