


Fiber Optic Cable - Multimode Duplex 62.5/125 - LSZH - SC/SC - 20 m

Product ID: FIBSCSC20



The FIBSCSC20 20-meter (65.6ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated at both ends with SC (male) connectors, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This SC-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our SC-SC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

Certifications, Reports and Compatibility

Applications

- Used by long distance networks with mission critical data
- Telecommunication/Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

Features

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

Hardware

Warranty	Lifetime
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Size	62.5/125

Performance

Fiber Classification	OM1
Type	Multi Mode

Connector(s)

Connector A	Fiber Optic SC Duplex
Connector B	Fiber Optic SC Duplex

Physical Characteristics

Color	Orange
Cable Length	65.6 ft [20 m]
Product Length	65.6 ft [20.0 m]

Packaging Information

Package Length	9.6 in [24.5 cm]
Package Width	1.0 in [24.3 mm]
Package Height	12.8 in [32.6 cm]
Shipping (Package) Weight	12.4 oz [350 g]

What's in the Box

Included in Package	20m MMode Duplex Fiber Optic Cable SC-SC
---------------------	--

****Product appearance and specifications are subject to change without notice.***

