

IEEE-1394 FireWire Adapter - 9 Pin to 6 Pin M/F

Product ID: FIRE96MF



The FIRE96MF IEEE-1394 FireWire 800 to 400 Adapter features a (male) FireWire 800 connector on one end and a (female) FireWire 400 connector on the other end, providing a cost-effective solution for connecting your older FireWire 400 devices to your FireWire 800-enabled devices or Mac family of products.

Supporting data transfer rates of up to 400Mbps, the FIRE96MF is great for applications requiring large file transfers, delivering a high speed link that minimizes data transfer time (e.g. transferring digital video files from a DV camcorder to a computer, etc).

Designed and constructed for both durability and convenience, the FireWire 800 to FireWire 400 Adapter (9-pin to 6-pin) is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Converts a 6-pin Firewire 400 cable for use with a 9-pin Firewire 800 device
- Plug and Play FireWire 400 devices with newer Mac devices and computers using FireWire 800 ports

Features

- Supports data transfer speeds up to 400 Mbps

- IEEE compliant
- Gold-plated connectors

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	1 - FireWire 800 (9 pin, IEEE 1394b)
Connector B	1 - FireWire 400 (6 pin, IEEE 1394a)

Physical Characteristics

Color	Black
Wire Gauge	26 AWG (0.404 mm)
Product Length	2.2 in [5.5 cm]
Product Width	0.6 in [1.5 cm]
Product Height	0.4 in [1 cm]
Weight of Product	0.4 oz [10 g]

Packaging Information

Package Quantity	1
Package Length	4.9 in [12.5 cm]
Package Width	3.5 in [90 mm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	0.4 oz [12 g]

What's in the Box

Included in Package	1 - IEEE-1394 FireWire Adapter - 9 Pin to 6 Pin M/F
---------------------	---

Warranty

Information

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***