

Flat-Screen TV Wall Mount - Tilting

Product ID: FLATPNLWALL



Maximize space while creating an impressive display with this flat-screen TV wall mount for large TVs or monitors. The heavy-duty wall mount securely supports a VESA Mount compliant TV from 32" to 75", with easy-to-use tilt adjustment for comfortable viewing.

Mount your flat-screen TV in a location that's convenient for visitors, clients and employees, while saving valuable space. The wall mount is ideal for boardrooms, lobbies or other venues providing an impressive and secure way to display a large flat-panel TV or create digital signage. The robust wall mount supports a large 32" to 75" flat-screen TV weighing up to 165 lb. (75 kg).

The TV wall mount lets you angle your TV display toward your audience. With the tilt feature, you can mount your TV lower or higher than eye level and still view it comfortably. The tilt-adjusting knobs make it easy to adjust your TV to the ideal viewing angle.

The hook-and-mount design of the TV wall mount makes setup fast and easy. You simply attach the vertical brackets, with built-in hooks, to the back of your TV. Once the brackets are attached, you then hang your TV securely onto the wall mount. Cable management helps to keep cables out of view.

The FLATPNLWALL is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Safely and securely wall-mount your TV
- Keep guests informed and entertained
- Ideal for lobbies, lecture halls, classrooms and meeting spaces

- Save space in your home theater or living room

Features

- Save space with this flat screen wall mount for 32" to 75" TVs up to 165 lb. (75 kg)
- Tilt your TV up or down (+15 to -15 degrees) for comfortable viewing
- Fits curved TVs, with compatible VESA mount
- Hook-and-mount design for easy setup with VESA compliant TVs
- Universal LCD/LED television mount supports LG, Samsung, Sony, Sharp, others (screws/spacers incl) & VESA bracket hole patterns 100x100, 100x200, 200x100, 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400

Hardware

Warranty	5 Years
Wallmountable	Yes
# of Displays Supported	1
Mounting Options	Wall-Mount
Minimum Profile from Wall	3.3 in [83 mm]
VESA Hole Pattern(s)	75x75 mm
	100x100 mm
	100x200 mm
	200x100 mm
	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm

400x400 mm

600X200 mm

600x300 mm

600x400 mm

Performance

Weight Capacity (Per Display)	165.8 lb [75 kg]
Minimum Display Size	32in
Maximum Display Size	75"
Video Wall	No
Fits Curved Display	Yes
Display Tilt	+ 15 / - 15
Anti-theft	No

Physical Characteristics

Color	Black
Material	Steel
Internal Width	31.9 in [81 cm]
Internal Height	19.7 in [50 cm]
Internal Depth	3.3 in [83 mm]
Product Length	31.9 in [81 cm]
Product Width	3.3 in [83 mm]
Product Height	19.7 in [50 cm]
Weight of Product	8.5 lb [3.8 kg]

Packaging Information

Package Length	32.9 in [83.5 cm]
----------------	-------------------



Package Width	9.4 in [23.8 cm]
Package Height	3.5 in [89 mm]
Shipping (Package) Weight	10.7 lb [4.9 kg]

What's in the Box

Included in Package	wall plate
	left bracket
	right bracket
	Allen key
	M5x14 mm screws
	M6x14 mm screws
	M8x30 mm screws
	M6x30 mm screws
	M8x50 mm screws
	washers
	short spacers
	long spacers
	6.3x55 mm screws
	concrete anchors
	flat washers
	instruction manual

****Product appearance and specifications are subject to change without notice.***

