

## Ceiling TV Mount - 8.2' to 9.8' Long Pole

**Product ID:** FPCEILPTBLP



This ceiling TV mount supports VESA mount compatible TVs from 32" to 75" in size, with a weight capacity of up to 110 lb. (50 kg). It lets you save wall and floor space by hanging your flat-panel LCD, LED or plasma TV from the ceiling in a prominent area.

The ceiling mount is ideal for use in lobbies, entrances or other areas with high ceilings.

With a telescopic pole, the TV mount lets you suspend a display at your desired distance from the ceiling. This works well with a range of ceiling heights. The steel pole can extend from 8.2 to 9.84 ft. (2.5 to 3 m), with a total lift (height extension) of 19.6" (.5 m).

The flat-screen ceiling mount accommodates a wide variety of ceiling types. You can swivel the TV to work with virtually any type of ceiling for level viewing, including sloped ceilings (up to 60 degrees), and pitched or horizontal (flat) ceilings.

You can adjust your TV to create a comfortable viewing angle, by tilting it up to -25 degrees down towards your audience for optimum visibility. Plus, the full-motion mount lets you swivel your display around the pole + 180 / - 180 degrees, without using tools.

Simply attach the included vertical brackets, with built-in hooks, to the back of your TV. Once attached, hang your TV securely onto the ceiling mount. The +/-3 degree post-installation leveling adjustments ensure ideal positioning after hanging.

FPCEILPTBLP is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

- Suspend a flat-screen TV in an area with a high ceiling
- Ideal for lobbies and entrance ways
- Keep your guests informed and entertained

## Features

- Save space by suspending your 32" to 75" flat-screen TV from the ceiling; Supports TVs up to 110 lb.(50 kg)
- Long pole with min-max length extension of 8.2 to 9.8' (2.5 to 3 m) for versatile use
- Ceiling TV mount swivels +60 /-60 degrees to adjust to sloped or level ceilings
- Full-motion mount lets you swivel the display +180 /-180 degrees around the pole and tilt downwards -25 degrees, without using tools
- Easy setup, with a hook-and-mount design
- Universal hanging TV ceiling mount supports LG, Samsung, Sony, and Sharp TVs among others (screws/spacers incl) & VESA hole patterns of 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400

---

## Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
# of Displays Supported	1
Mounting Options	Ceiling Mount
VESA Hole Pattern(s)	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm



600X200 mm

600x300 mm

600x400 mm

---

**Performance**

General Specifications	Post-Installation Leveling Adjustment: +/-3
Weight Capacity (Per Display)	110.5 lb [50 kg]
Minimum Display Size	32in
Maximum Display Size	75"
Video Wall	No
Fits Curved Display	Yes
Height Adjustment	Yes
Minimum Height	8.2 ft [2.5 m]
Maximum Height	9.8 ft [3 m]
Display Tilt	+0 / -25
Swivel / Pivot	+180 to -180
Anti-theft	No

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	26.8 in [68.0 cm]
Product Width	17.1 in [43.5 cm]
Product Height	10.6 ft [3.2 m]
Weight of Product	22.1 lb [10.0 kg]

---

**Packaging Information**



Package Length	4.2 ft [1.3 m]
Package Width	12.6 in [32.0 cm]
Package Height	4.5 in [11.5 cm]
Shipping (Package) Weight	24.0 lb [10.8 kg]

---

**What's in the Box**

Included in Package	ceiling mount and pole
	middle pole
	lower pole
	TV mount
	vertical brackets
	horizontal bracket
	M8x55 mm screws
	M8x60 mm screws
	nuts
	wrench
	hex key
	mounting template
	M5x14 mm screws
	M6x14 mm screws
	M6x30 mm screws
	M8x30 mm screws
	M8x50 mm screws
	rectangular washers
	small spacers
	large spacers



screws

concrete anchors

circular washers

instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

