

## Low-Profile TV Wall Mount - Fixed

Product ID: FPWFXBAT



Save space while improving the appearance of your work area, with this low-profile TV wall mount. The mount sits close to the wall to support a VESA Mount compliant TV from 37" to 75", and offers anti-theft protection.

Mount your flat-screen TV or monitor in a location that's convenient for visitors, clients or employees. The wall mount safely and securely supports your TV in a fixed position, less than an inch (22 mm) from the wall, to provide a sleek, low-profile look.

It's ideal for lobbies, hallways, boardrooms, works areas, customer-facing areas or for creating digital signage. The wall mount supports most 37" to 75" (940 to 1905mm) LED or LCD flat panel TVs weighing up to 88 lb. (40 kg).

Engineered with heavy-duty steel, the robust steel TV wall mount securely supports your flat-screen TV, to protect your investment. Ideal for areas with high traffic and minimal supervision, the TV mount features a steel bar that can be locked into place with a padlock (purchased separately) to deter theft of your equipment.

A built-in level helps to ensure your TV is aligned in a straight position on your wall, to ensure optimum viewing.

The FPWFXBAT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Securely wall-mount a TV
- Keep guests informed and entertained
- Ideal for classrooms, lecture halls or customer-facing areas

- Deter theft of your TV or monitor

## Features

- Save space with this flat-screen TV wall mount for 37" to 75" TVs
- Low profile TV mount sits less than 1" (only 22 mm) from the wall
- Stays in fixed position, with built-in level to ensure ideal position during installation
- Heavy-duty steel TV wall mount supports up to 40 kg (88 lb.)
- Lockable bar securely holds TV and deters theft (padlock required)

<b>Hardware</b>	Warranty	5 Years
	Cable Management	No
	Articulating	No
	# of Displays Supported	1
	Mounting Options	Wall-Mount
	Minimum Profile from Wall	0.9 in [22 mm]
	VESA Hole Pattern(s)	300x300 mm
	VESA Hole Pattern(s)	400x200 mm
	VESA Hole Pattern(s)	400x400 mm
	VESA Hole Pattern(s)	600x400 mm
	VESA Hole Pattern(s)	800x400 mm
	VESA Hole Pattern(s)	200x200 mm
<b>Performance</b>	Weight Capacity (Per Display)	88.4 lb [40 kg]
	Minimum Display Size	37"
	Maximum Display Size	75"
	Fits Curved Display	Yes
	Video Wall	No
	Anti-theft	Yes
	<b>Physical Characteristics</b>	Color
Material		Steel
Product Length		35.4 in [9.0 cm]
Product Width		1.1 in [29.000 mm]
Product Height		17.3 in [4.4 cm]

Weight of Product 6.4 lb [2.9 kg]

---

**Packaging Information**

Package Length	38.5 in [9.8 cm]
Package Width	9.3 in [2.4 cm]
Package Height	1.9 in [49.000 mm]
Shipping (Package) Weight	8.5 lb [3.9 kg]

---

**What's in the Box**

Included in Package	wall mount
Included in Package	safety bar
Included in Package	adapter brackets
Included in Package	level
Included in Package	decorative covers
Included in Package	decorative cover screws
Included in Package	M5x14 mm screws
Included in Package	M6x14 mm screws
Included in Package	M8x50 mm screws
Included in Package	M6x30 mm screws
Included in Package	M8x30 mm screws
Included in Package	rectangular washers
Included in Package	small spacers
Included in Package	large spacers
Included in Package	screws
Included in Package	concrete anchors
Included in Package	circular washers
Included in Package	instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

