

Triple-Display TV Wall Mount - Menu Board Mount - Landscape

Product ID: FPWMNB



Create a perfectly aligned menu board with this triple-display TV wall mount for 40" to 50" displays. The modular wall-mounting system is easy to set up. Adjust the tilt for all three displays at the same time, and fine-tune the screen level with ease.

Digital menu boards are a great way to increase customer sales, promote new offerings, and inform customers at the point of sale. Ideal for restaurants, retail stores and many other businesses, this professional-grade menu board mount supports three 40" to 50" VESA mount TVs in landscape position. It supports a weight capacity of 110 lb. (50 kg) per display, and is compatible with VESA 200x200, 300x200, 300x300, 400x200, 400x300, 400x400, and 600x400.

For optimum viewing, you can adjust the tilt of all three displays to the same angle simultaneously, without using tools. The multi-screen mount has five fixed tilt settings: 0/-5/-10/-15/-20.

To ensure precise alignment of all three TVs, you can fine-tune the level of the displays +3 to -3 using the micro height adjustment feature.

With its heavy-duty steel construction, the triple-monitor wall bracket provides durable performance.

Save time on setup. The hook-and-mount design of the triple-display wall mount makes installation fast and easy.

FPWMNB is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for digital menu boards in restaurants and retail stores
- Create digital signage in customer-facing areas in business lobbies, airports and hospitality centers
- Communicate with visitors in schools, health care centers and other institutional settings

Features

- Create a digital menu board, mounting three 40" to 50" TVs in landscape position
- Tilt all displays to the same angle easily, with five fixed-tilt settings: 0/-5/-10/-15/-20
- Align your displays with micro height adjustment, fine-tuning the screen level +3 to -3
- 3.0" (76 mm) profile to wall, and fast and easy installation
- Steel mount supports VESA 200x200, 300x200, 300x300, 400x200, 400x300, 400x400, 600x400, and up to 110 lb. (50 kg) weight per display

Hardware	Warranty	5 Years
	Wallmountable	Yes
	Cable Management	No
	VESA Hole Pattern(s)	200x200 mm
	VESA Hole Pattern(s)	300x300 mm
	VESA Hole Pattern(s)	400x200 mm
	VESA Hole Pattern(s)	400x300 mm
	VESA Hole Pattern(s)	600x400 mm
	VESA Hole Pattern(s)	300x200 mm
	VESA Hole Pattern(s)	400x400 mm
Performance	General Specifications	Screen Level Adjustment: +3 to -3
	Weight Capacity (Per Display)	110.5 lb [50 kg]
	Minimum Display Size	40"
	Maximum Display Size	50"
	Fits Curved Display	No
	Video Wall	No
	Display Tilt	0 / -5 / -10 / -15 / -20
	Anti-theft	No
Physical Characteristics	Color	Black
	Material	Steel
	Product Length	9.5 ft [2.9 m]

Product Width	3.1 in [78.000 mm]
Product Height	8.9 in [2.2 cm]
Weight of Product	31.5 lb [14.2 kg]

Packaging Information

Package Length	29.1 in [7.4 cm]
Package Width	9.8 in [2.5 cm]
Package Height	9.1 in [2.3 cm]
Shipping (Package) Weight	35.4 lb [16.0 kg]

What's in the Box

Included in Package	Wall Plates
Included in Package	Small Wall Plate
Included in Package	Adapter Brackets
Included in Package	Wall Plate Clamps
Included in Package	M4 x 6 mm Screws
Included in Package	Safety Pins
Included in Package	M5 x 14 mm Screws
Included in Package	M6 x 14 mm Screws
Included in Package	M6 x 30 mm Screws
Included in Package	M8 x 30 mm Screws
Included in Package	M8 x 50 mm Screws
Included in Package	Plate Washers
Included in Package	Small Spacers
Included in Package	Large Spacers
Included in Package	ST6.3 x 55 mm Screws
Included in Package	Concrete Anchors
Included in Package	D6 Washers
Included in Package	User Manual
Included in Package	5 mm Hex Key

****Product appearance and specifications are subject to change without notice.***

