

## Triple-Display TV Wall Mount - Menu Board Mount - Landscape

**Product ID:** FPWMNB



Create a perfectly aligned menu board with this triple-display TV wall mount for 40" to 50" displays. The modular wall-mounting system is easy to set up. Adjust the tilt for all three displays at the same time, and fine-tune the screen level with ease.

Digital menu boards are a great way to increase customer sales, promote new offerings, and inform customers at the point of sale. Ideal for restaurants, retail stores and many other businesses, this professional-grade menu board mount supports three 40" to 50" VESA mount TVs in landscape position. It supports a weight capacity of 110 lb. (50 kg) per display, and is compatible with VESA 200x200, 300x200, 300x300, 400x200, 400x300, 400x400, and 600x400.

For optimum viewing, you can adjust the tilt of all three displays to the same angle simultaneously, without using tools. The multi-screen mount has five fixed tilt settings: 0/-5/-10/-15/-20.

To ensure precise alignment of all three TVs, you can fine-tune the level of the displays +3 to -3 using the micro height adjustment feature.

With its heavy-duty steel construction, the triple-monitor wall bracket provides durable performance.

Save time on setup. The hook-and-mount design of the triple-display wall mount makes installation fast and easy.

FPWMNB is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Ideal for digital menu boards in restaurants and retail stores
- Create digital signage in customer-facing areas in business lobbies, airports and hospitality centers
- Communicate with visitors in schools, health care centers and other institutional settings

## Features

- Create a digital menu board, mounting three 40" to 50" TVs in landscape position; Supports up to 110 lb. (50 kg) in weight per display
- Tilt all displays to the same angle easily, with five fixed-tilt settings: 0/-5/-10/-15/-20
- Align your displays with micro height adjustment, fine-tuning the screen level +3 to -3
- 3.0" (76 mm) profile to wall, and fast and easy installation
- Universal LCD/LED television mount supports LG, Samsung, Sony, Sharp, others (screws/spacers incl) & VESA bracket hole patterns 200x100, 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400

---

### Hardware

Warranty	5 Years
Wallmountable	Yes
Cable Management	No
VESA Hole Pattern(s)	200x100 mm
	300x300 mm
	200x200 mm
	200x300 mm
	200x400 mm
	400x200 mm
	300x200 mm
	400x300 mm
	400x400 mm
	600X200 mm

600x300 mm

600x400 mm

## Performance

General Specifications	Screen Level Adjustment: +3 to -3
Weight Capacity (Per Display)	110.2 lb [50 kg]
Minimum Display Size	40"
Maximum Display Size	50"
Fits Curved Display	No
Video Wall	No
Display Tilt	0 / -5 / -10 / -15 / -20
Anti-theft	No

## Physical Characteristics

Color	Black
Material	Steel
Product Length	9.5 ft [2.9 m]
Product Width	3.1 in [7.8 cm]
Product Height	8.9 in [22.5 cm]
Weight of Product	31.4 lb [14.2 kg]

## Packaging Information

Package Quantity	1
Package Length	9.9 in [25.1 cm]
Package Width	29.5 in [74.9 cm]
Package Height	9.4 in [23.8 cm]
Shipping (Package) Weight	35.5 lb [16.1 kg]

---

## What's in the Box

Included in Package	4 - Wall Plates
	1 - Small Wall Plate
	6 - Adapter Brackets
	8 - Wall Plate Clamps
	6 - Safety Pins
	16 - M4 x 6 mm Screws
	12 - M5 x 14 mm Screws
	12 - M6 x 14 mm Screws
	12 - M6 x 30 mm Screws
	12 - M8 x 30 mm Screws
	12 - M8 x 50 mm Screws
	12 - Plate Washers
	24 - Small Spacers
	24 - Large Spacers
	18 - ST6.3 x 55 mm Screws
	18 - Concrete Anchors
	18 - D6 Washers
	1 - 5 mm Hex Key
	1 - User Manual

---

***\*Product appearance and specifications are subject to change without notice.***