

Low-Profile TV Wall Mount - Tilting

Product ID: FPWTLTBAT



Save space while improving the appearance of your work area, with this low-profile TV wall mount. The mount sits close to the wall to support a VESA Mount compliant TV from 37" to 75", and offers theft deterrence as well as tilting capability that makes it easy to find the perfect viewing position.

Mount your flat-screen TV or monitor in a location that's convenient for visitors, clients or employees. The wall mount safely and securely supports your TV about two inches (51 mm) from the wall to provide a sleek, low-profile look.

It's ideal for lobbies, hallways, boardrooms, works areas, customer-facing areas or for creating digital signage. The wall mount supports most 37" to 75" (940 to 1905 mm) LED or LCD flat panel TVs weighing up to 88 lb. (40 kg).

This TV wall mount tilts -10 to +5 degrees, so you can adjust the angle of your display with ease to customize your viewing experience.

Engineered with heavy-duty steel, the robust steel TV wall mount securely supports your flat-screen TV, to protect your investment. Ideal for areas with high traffic and minimal supervision, the TV mount features a steel bar that can be locked into place with a padlock (purchased separately) to deter theft of your equipment.

A built-in level helps to ensure your TV is aligned in a straight position on your wall, to ensure optimum viewing.

The FPWTLTBAT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Securely wall-mount a TV
- Keep guests informed and entertained
- Ideal for classrooms, lecture halls or customer-facing areas
- Deter theft of your TV or monitor

Features

- Save space with this flat-screen TV wall mount for 37" to 75" TVs (fits curved TVs, with compatible VESA mount)
- Low profile TV mount sits only 2" (51 mm) from the wall
- Heavy-duty steel TV wall mount (tool-less assembly) supports up to 88 lb. (40 kg)
- Tilts -10 to +5 degrees for optimal viewing
- Lockable bar securely holds TV and provides theft deterrence (padlock required)

Hardware	Warranty	5 Years
	Cable Management	No
	Articulating	No
	# of Displays Supported	1
	Mounting Options	Wall-Mount
	Minimum Profile from Wall	2.0 in [51 mm]
	VESA Hole Pattern(s)	200x200 mm
	VESA Hole Pattern(s)	300x300 mm
	VESA Hole Pattern(s)	400x200 mm
	VESA Hole Pattern(s)	400x400 mm
	VESA Hole Pattern(s)	600x400 mm
	VESA Hole Pattern(s)	800x400 mm
Performance	Weight Capacity (Per Display)	88.4 lb [40 kg]
	Minimum Display Size	37"
	Maximum Display Size	75"
	Fits Curved Display	Yes
	Video Wall	No
	Anti-theft	Yes
	Physical Characteristics	Material
Product Length		39.3 in [10.0 cm]
Product Width		2.0 in [51.000 mm]

Product Height	17.3 in [4.4 cm]
Weight of Product	8.1 lb [3.7 kg]

Packaging Information	Package Length	38.9 in [9.9 cm]
	Package Width	9.3 in [2.4 cm]
	Package Height	2.6 in [65.000 mm]
	Shipping (Package) Weight	10.5 lb [4.8 kg]

What's in the Box	Included in Package	wall mount
	Included in Package	safety bar
	Included in Package	left adapter bracket
	Included in Package	right adapter bracket
	Included in Package	level
	Included in Package	decorative covers
	Included in Package	decorative cover screws
	Included in Package	M5x14 mm screws
	Included in Package	M6x14 mm screws
	Included in Package	M8x50 mm screws
	Included in Package	M6x30 mm screws
	Included in Package	M8x30 mm screws
	Included in Package	rectangular washers
	Included in Package	small spacers
	Included in Package	large spacers
	Included in Package	screws
	Included in Package	concrete anchors
	Included in Package	circular washers
Included in Package	instruction manual	

****Product appearance and specifications are subject to change without notice.***

