

10ft (3m) Heavy Duty Extension Cord, C14 to C15 Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, Heavy Duty AC Power Cord

Produkt-ID: H1415-10F-POWER-CORD



The H1415-10F-POWER-CORD features a C15 connector rated for high-temperature equipment. The cable is 14 AWG which is suitable for high power connections.

A reliable solution for connecting to C14 Power Distribution Units (PDUs), located in switchgear rooms and data center environments, or large server applications requiring a high voltage/amperage, heavy gauge cable.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **HEAVY DUTY EXTENSION CORD:** This 10ft (3m) 14AWG universal power cord with IEC 60320 C14 to IEC 60320 C15 connectors is suitable for workstations/home office; Indoor use; Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** Made with UL-listed components (UL62 & UL817); Fully molded strain

relief on connectors for durability; Fire Rating: VW-1; 3 Conductor Power cable made with 100% copper wire; ETL Certified; Available in 3ft and 6ft length

- SPECS: 10ft (3m) AC Power Cord; IEC 60320 C14 to IEC 60320 C15; 14AWG; 125V 15A (Max); Jacket Type: SJT; Jacket Material: PVC; Black; Temperature Range: -4°to 140°F (-20 to 60°C); Cable Outer Diameter: 0.34in (8.7mm)
- COMPATIBILITY: PC Power Cord C14 works with most computer hardware; Extend connections to servers, desktop computers, monitors, printers, and more; Replacement power extension cable/cord
- DIE BEVORZUGTE WAHL DES IT-PROFIS: Entwickelt und erstellt für Computerfachleute, ist dieser Verlängerungskabel Lebenslang unterstützt, inklusive kostenlosem, lebenslangem, mehrsprachigem technischem Support (24/5).

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandssklasse	Klasse VW-1e
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - IEC 60320 C14 Strom
Steckverbinder B	1 - IEC 60320 C15 Strom

Strom

Eingangsspannung	125V AC
Eingangsstrom	15 A

Umgebungsbedingungen

Betriebstemperatur	-20 to 60°C (-4 to 140°F)
Lagertemperatur	0 to 30°C (32 to 86°F)
Feuchtigkeit	5%~95%

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	14 AWG
Kabellänge	120.1 in [3050 mm]
Außendurchmesser des Kabels	0.3 in [8.7 mm]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	1.1 in [2.8 cm]
Produkthöhe	0.8 in [2.0 cm]
Produktgewicht	15.3 oz [434.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.2 in [18.3 cm]
Paketbreite	9.6 in [24.5 cm]
Pakethöhe	2.1 in [5.4 cm]
Versandgewicht (Verpackung)	15.9 oz [450.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - Netzkabel
--------------------	---------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.