

10ft (3m) Heavy Duty Extension Cord, C14 to C15 Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, Heavy Duty AC Power Cord

Product ID: H1415-10F-POWER-CORD



The H1415-10F-POWER-CORD features a C15 connector rated for high-temperature equipment. The cable is 14 AWG which is suitable for high power connections.

A reliable solution for connecting to C14 Power Distribution Units (PDUs), located in switchgear rooms and data center environments, or large server applications requiring a high voltage/ampereage, heavy gauge cable.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **HEAVY DUTY EXTENSION CORD:** This 10ft (3m) 14AWG universal power cord with IEC 60320 C14 to IEC 60320 C15 connectors is suitable for workstations/home office; Indoor use; Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** Made with UL-listed components (UL62 & UL817); Fully molded strain relief on connectors for durability; Fire Rating: VW-1; 3 Conductor Power cable made with 100% copper wire; ETL Certified; Available in 3ft and 6ft length

- **SPECS:** 10ft (3m) AC Power Cord; IEC 60320 C14 to IEC 60320 C15; 14AWG; 125V 15A (Max); Jacket Type: SJT; Jacket Material: PVC; Black; Temperature Range: -4to 140F (-20 to 60C); Cable Outer Diameter: 0.34in (8.7mm)
- **COMPATIBILITY:** PC Power Cord C14 works with most computer hardware; Extend connections to servers, desktop computers, monitors, printers, and more; Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C15 Power

Power

Input Voltage	125V AC
Input Current	15 A

Environmental

Operating Temperature	-20 to 60C (-4 to 140F)
Storage Temperature	0 to 30C (32 to 86F)
Humidity	<55%RH

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	120.1 in [3050 mm]
Cable OD	0.3 in [8.7 mm]

Product Length	10.0 ft [3.0 m]
Product Width	1.1 in [2.8 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	15.3 oz [434.0 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	9.8 in [25.0 cm]
Package Height	2.0 in [5.0 cm]
Shipping (Package) Weight	16.0 oz [452.0 g]

What's in the Box

Included in Package	1 - Power Cord
---------------------	----------------

**Product appearance and specifications are subject to change without notice.*