

Desk Mount Monitor Arm, Up To 32" Display, Max 22lb/10kg, VESA 75x75/100x100, C-Clamp, Fully Articulating, Mechanical Spring, TAA-compliant

Product ID: H1M1AG2-MONITOR-ARM



This monitor desk mount is designed to support up to a 32-inch ultrawide display, creating an ergonomic area for productivity. The mechanical spring-assisted arm enables multiple adjustment to suit different ergonomic needs.

The monitor arm comes pre-assembled and includes a VESA monitor plate that uses thumb screws to securely mount the monitor quickly and without additional tools.

The mechanical spring arm enables toolless height adjustment with a range from 7.7 to 20.6in (19.7 to 52.4cm) with effortless one-touch motion. The maximum arm extension is 21in (53.5cm) with a total weight capacity of 22lb (10kg).

The monitor's VESA mounts enable support of +/-15 swivel, +90/-15 tilt, and 360 screen rotation for portrait/landscape orientation.

To maintain an organized workspace, the arms feature a cable management channel along the underside to keep cables out of sight, reducing clutter and contributing to a tidy setup.

The monitor mount is TAA-compliant and is backed for 10-years including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **DESK MOUNT MONITOR ARM:** Single monitor mount supports up to 32-inch widescreen display, max 22lb (10kg); VESA plate supports 75x75/100x100mm patterns; Articulating and height adjustable mechanical spring arm; TAA-compliant
- **QUICK AND TOOLLESS INSTALLATION:** Premium monitor arm ships pre-assembled & features a VESA plate with thumb screws for tool-less monitor mounting; C-clamp comes with hand knob for ease of installation, supports desk thickness from 0.8 to 2.3in (2 to 6cm)
- **MECHANICAL SPRING ONE-TOUCH ADJUSTMENT:** Full-motion arm features a high-quality mechanical spring for smooth and effortless one-touch motion; Mechanical springs are more robust and resistant to wear over time compared to gas springs; Backed for 10 years
- **DISPLAY ADJUSTMENT:** Ergonomic monitor mount with toolless adjustments of +/-15 swivel, +90/-15 tilt, & 360 screen rotation (portrait/landscape); Max arm extension 21in (53.5cm), height range of 7.7 to 20.6in (19.7 to 52.4cm)
- **ORGANIZED WORKSPACE:** Monitor mount features integrated cable management channels along the arms, ensuring that all cables are neatly organized and out of sight

Hardware

Warranty	10 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.8 - 2.3in (2 - 6cm)

Performance

Weight Capacity (Per Display)	22.0 lb [10 kg]
Minimum Display Size	17"
Maximum Display Size	32"

Fits Curved Display	No
Fits UltraWide Displays	No
Height Adjustment	Yes
Minimum Height	8.0 in [202 mm]
Maximum Height	20.8 in [529 mm]
Minimum Arm Extension	6.3 in [160 mm]
Maximum Arm Extension	22.6 in [574 mm]
Display Tilt	+65 / -15
Display Swivel	+/-15
Swivel / Pivot	+180 / -180
Display Rotation	360
Anti-theft	No

Physical Characteristics

Color	Black
Construction Material	Aluminum, Steel, and Plastic
Product Length	21.7 in [55 cm]
Product Width	13.6 in [34.5 cm]
Product Height	23.0 in [58.3 cm]
Weight of Product	6.7 lb [3.0 kg]

Packaging Information

Package Length	13.4 in [34.0 cm]
Package Width	21.5 in [54.7 cm]
Package Height	6.5 in [16.4 cm]
Shipping (Package) Weight	7.7 lb [3.5 kg]

What's in the Box

Included in Package	1 - Arm Assembly
	2 - Base (EVA Cushion)
	1 - VESA Monitor Mount
	4 - VESA Screws
	1 - M3 Hex Key
	1 - M6 Hex Key
	1 - Cable Clip
	1 - Quick-Start Guide

**Warranty
Information**

Warranty	10 Years
----------	----------

**Product appearance and specifications are subject to change without notice.*