

Travel A/V Adapter: 3-in-1 HDMI to DisplayPort, VGA or DVI - 1920 x 1200

Product ID: HD2DPVGDVI



This travel adapter lets you connect your HDMI enabled Ultrabook or laptop computer to any DisplayPort, VGA or DVI display. To ensure compatibility with your computer, the adapter has been engineered to support both Windows and Mac computers.

This 3-in-1 adapter gives you all the video outputs you need to connect to any projector or display. With DisplayPort, VGA and DVI outputs, this adapter lets you connect from your laptop's HDMI port to any boardroom or classroom display, without the inconvenience of carrying a separate adapter for each display type.

With support for multiple video outputs and a lightweight, small-footprint design, this adapter is the perfect solution for traveling professionals, such as sales representatives or instructors. The 3-in-1 A/V adapter is also great for BYOD (Bring Your Own Device) applications around the office.

The adapter features plug-and-play installation, enabling you to quickly and easily connect to almost any display you come across, so you can focus on the finer details of your presentation and not the technical details of a boardroom's A/V setup. It's USB powered, which means a power adapter is not required, making the adapter easier to carry. Plus, you can just plug the adapter into your computer, instead of having to find an additional power source.

The DisplayPort output on this adapter supports Ultra HD 4K resolutions, providing four times the picture quality of high-definition 1080p. The DP output is also backward compatible with lower resolutions, such as 1080p and 720p, so the adapter is also perfect for your legacy video equipment. The VGA and DVI outputs also support a high-definition maximum resolution up to 1920 x 1200, so you can still enjoy excellent video quality.

The HD2DPVGDVI is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD Ultrabook to a provided DisplayPort, VGA or DVI display at work
- Use a DisplayPort, VGA or DVI display as a secondary monitor

Features

- 3-in-1 adapter - HDMI to DisplayPort, HDMI to VGA, HDMI to DVI
- Maximize portability, with a USB-powered video adapter
- Astonishing picture quality, with support for UHD 4K
- Plug-and-play installation
- Lightweight design
- Small footprint

Hardware

Warranty	2 Years
----------	---------

Active or Passive Adapter	Active
---------------------------	--------

	Passive
--	---------

AV Input	HDMI
----------	------

AV Output	DisplayPort
-----------	-------------

	DVI
--	-----

	VGA
--	-----

Audio	Yes
-------	-----

Performance

Video Revision	DisplayPort 1.2
----------------	-----------------

Maximum Analog Resolutions	1920 x 1200
----------------------------	-------------

Maximum Digital Resolutions	3840 x 2160 (4K x 2K) @ 30 Hz (DisplayPort)
-----------------------------	---

Supported Resolutions	DisplayPort: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720 VGA: 1920 x 1200, 1920 x 1080, 1280 x 720 DVI: 1920 x 1200, 1920 x 1080, 1280 x 720
Wide Screen Supported	Yes
Audio Specifications	DP output - 2-channel stereo
General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
MTBF	858,339 hours

Connector(s)

Connector Type(s)	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector A	1 - HDMI (19 pin)
Connector B	1 - DisplayPort (20 pin) 1 - VGA (15 pin, High Density D-Sub) 1 - DVI-I (29 pin)

Special Notes / Requirements

Note	The DisplayPort output is an active port. The VGA output is an active port. The DVI-D output is a passive port.
------	---

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 55C (14F to 131F)
Humidity	40~50% RH

Physical Characteristics

Cable Length	8.2 in [209.6 mm]
--------------	-------------------

Product Length	11.8 in [30.0 cm]
Product Width	2.2 in [5.5 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Quantity	1
Package Length	6.7 in [17.0 cm]
Package Width	5.7 in [14.4 cm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	4.9 oz [138.0 g]

What's in the Box

Included in Package	1 - travel A/V adapter
	1 - quick start guide

****Product appearance and specifications are subject to change without notice.***