

## HDMI to VGA Converter with Audio - Compact - 1920x1200

**Product ID:** HD2VGAMICRA



This HDMI to VGA adapter lets you connect your HDMI computer to a VGA display or projector. The versatile adapter features a discrete 3.5mm audio output for extracting stereo audio from your HDMI signal, and supports PC resolutions up to 1920x1200.

The adapter works with any HDMI equipped computer to add compatibility with VGA displays. Enabling VGA support on your Ultrabook or Chromebook means that you'll have the connection options you need to use almost any boardroom projector or display.

The HDMI to VGA adapter doesn't require software or drivers, which saves you time and hassle when you need to make a quick connection. Plus, the adapter features a 3.5mm output which gives you the option to share the audio directly from your HDMI port.

This compact HDMI to VGA adapter is lightweight and portable, and easily fits into any laptop carrying bag. The adapter has also been engineered with low-power architecture, so you won't need to carry a bulky external power adapter, or find access to an electrical outlet while you're on the go.

This converter will not output digitally encrypted content.

The HD2VGAMICRA is backed by a 3-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility





## Applications

- Connect your Ultrabook or Chromebook to a boardroom display
- Use your VGA monitor as secondary display
- Carry the adapter with you while travelling to ensure your laptop is compatible with VGA displays in BYOD applications

## Features

- Increase the compatibility of your HDMI equipped Ultrabook or Chromebook by adding support for VGA
- Hassle-free setup, through plug-and-play installation
- Maximum portability with a small foot print and lightweight design
- Supports resolutions up to 1920x1200 (1080p)
- Discrete 3.5mm audio output

---

### Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	HDMI
Ports	1
AV Output	VGA
Audio	Yes
Chipset ID	Chrontel - CH7101A-BF

---

### Performance

Maximum Digital Resolutions	1900x1200 @ 60Hz
Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720

Standard(16/32 bit):

1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864,  
1024x768, 800x600

Wide Screen Supported Yes

Audio Specifications 2-channel stereo (3.5mm)

---

**Connector(s)**

Connector A 1 - HDMI (19 pin)

Connector B 1 - VGA (15 pin, High Density D-Sub)

1 - 3.5 mm Mini-Jack (3 Position)

---

**Special Notes / Requirements**

Note This converter is not compatible with Mac computers that use Intel HD 4000 cards (Mac Mini), for specific support for these devices StarTech.com offers the Mac Mini to VGA adapter - [MCHD2VGA](https://www.startech.com/AV/Converters/Video/HDMI-HD-MI-Micro-to-VGA-Adapter-Converter-HDMI-Tablet-to-Monitor-MCHD2VGA).

This converter will not output digitally encrypted content.

---

**Environmental**

Operating Temperature 10C to 40C (50F to 104F)

Storage Temperature -20C to 70C (-4F to 158F)

Humidity 90% RH

---

**Physical Characteristics**

Color Black

Product Length 2.5 in [6.2 cm]

Product Width 0.8 in [2.1 cm]

Product Height 0.5 in [1.2 cm]

Weight of Product 0.3 oz [8.0 g]

---

**Packaging  
Information**

Package Length	5.8 in [14.8 cm]
Package Width	3.2 in [8.2 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	1.5 oz [42.0 g]

---

**What's in the Box**

Included in Package	1 - Compact HDMI to VGA adapter
---------------------	---------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***