

5m / 16 ft CL3 Rated HDMI Cable w/ Ethernet - In Wall Rated Ultra HD HDMI Cable - 4K 30Hz UHD High Speed HDMI Cable - 10.2 Gbps - HDMI 1.4 Video/Display Cable - 30AWG, White

Product ID: HD3MM5MW



The HD3MM5MW 5m (16ft) High Speed HDMI Cable is CL3-Rated for in-wall installations, and features two gold-plated HDMI (male) connectors to provide a dependable high quality HDMI to HDMI connection between devices such as Blu-Ray Disc players, HDTVs, DVD Players, stereo receivers, projectors and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HD3MM5MW 5-meter in-wall HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Certifications, Reports and Compatibility



Applications

- In-wall HDMI cable runs
- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles,

projectors etc.

Features

- **HIGH SPEED HDMI CABLE:** 16.4 ft (5 m) HDMI 1.4b Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE CL3 RATED CABLE:** Ultra HD HDMI cable with durable PVC jacket and strain relief for high strength and reliability; CL3 rated jacket releases low levels of toxic fumes in case of fire; Ideal for in-wall installations & for Commercial environments
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 16.4 ft (5 m) White HDMI 1.4b HDMI Cord Male to Male 30 AWG Gold-plated connectors PVC Jacket, CL3 Rated Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 & earlier

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CL3 Rated

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical Characteristics

Color	White
Connector Style	Straight

Wire Gauge	30/32 AWG
Cable Length	16.4 ft [5 m]
Product Length	16.4 ft [5.0 m]
Product Width	0.8 in [20.5 mm]
Product Height	0.4 in [1.1 cm]
Weight of Product	7.7 oz [218.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.6 in [15.0 mm]
Shipping (Package) Weight	8.0 oz [228.0 g]

What's in the Box

Included in Package	1 - 5m White CL3 High Speed HDMI Cable - M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***