

3m (10ft) Premium Certified High Speed HDMI Cable, 4K 60Hz/1440p 144Hz, HDR10/HDCP 2.2/ARC, 18Gbps, UHD HDMI 2.0 Cord for TV/Monitor/Display, TPE Jacket

Product ID: HDMI2-CABLE-4K60-3M



Connect to a 4K UHD TV or monitor, using this Premium Certified HDMI® 2.0 Cable. The connector markings enable quick visual identification, distinguishing this cable from other similar-looking or unmarked HDMI cables. Eliminate guesswork and always choose the appropriate cable to support full HDMI 2.0 with Ethernet capabilities.

For seamless operation between HDMI-enabled devices, the Premium HDMI® Cable is Certified for guaranteed HDMI 2.0 performance and backward compatibility. Certified cables provide consistent, reliable performance across multiple resolutions and refresh rates.

This High Speed HDMI® Cable features a flexible TPE outer jacket that is tested to withstand 2,000 bending cycles at +/-60 degrees, and routes easily around corners and desk edges. Robust strain reliefs enable convenient positioning of the cable. The durable Gold-plated connectors are rated to operate beyond 10,000 insertions.

This Certified HDMI Cable supports full HDMI 2.0 features:

- Resolutions up to 4K 60Hz using a compatible HDMI source and display
- Supports high refresh rates including 1440p 144Hz and 1080p 240Hz
- 21:9 Aspect Ratio support for cinematic viewing experiences
- High Dynamic Range (HDR10) for higher contrast ratio and vibrant picture quality
- High-Bandwidth Digital Content Protection (HDCP) 2.2 for a secure connection between source and display
- Audio Return Channel (ARC) for sending audio from the TV back to an AV receiver or soundbar
- Up to 32 Uncompressed Digital Audio Channels
- HDMI Ethernet Channel (HEC) for network connectivity over HDMI

- Backward compatible with previous HDMI versions

This HDMI 2.0 Cable is constructed with braided aluminum mylar shielding to minimize EMI for clear, consistent audio/video output and long-term reliable performance.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

Features

- **HIGH PERFORMANCE:** Premium Certified HDMI 2.0 Cable is designed for UHD-enabled HDMI devices; Choose the right HDMI cable at-a-glance with performance markings on connectors for quick and easy identification; Up to 18Gbps for seamless 4K 60Hz video
- **CERTIFIED:** Premium HDMI Cable is certified for guaranteed HDMI 2.0 performance and compatibility, ensuring reliable signal consistency and smooth video playback on any HDMI display; Backward compatible with earlier HDMI versions
- **QUALITY CONSTRUCTION:** Gold-plated connectors rated beyond 10,000 insertions; Durable TPE Jacket and strain reliefs are halogen-free and RoHS compliant; Tested to withstand 2,000 bending cycles at +/-60 degrees; Braided shield for enhanced EMI protection
- **APPLICATIONS:** Ideal for 4K UHD displays; Up to 144Hz refresh rate at 1440p resolution; Suitable for high performance GPUs and workstations; Connect an HDMI monitor to a 4K docking station
- **SPECS:** Black; 3-meter (9.8-foot); Premium Certified HDMI with Ethernet; HDMI 2.0 supports HDR10/ARC/ HDCP 2.2/CEC; 4K 60Hz/1440p 144Hz/1080p 240Hz; 18Gbps; 32-ch Audio; Backward Compatible; 30AWG; 6mm (0.24in) O.D.

General

UPC	065030910521
Warranty	Lifetime

Physical & Environmental

Color	Black
-------	-------

Material	Santoprene - Thermoplastic Rubber (TPE)
Connector Style	Straight
Cable Length	10.0 ft [3.0 m]
Cable OD	0.2 in [6 mm]
Product Length	9.9 ft [3.0 m]
Product Width	0.8 in [20.5 mm]
Product Height	0.4 in [10.7 mm]
Weight of Product	4.5 oz [128.0 g]
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Humidity	10% to 90%

Performance

Maximum Data Transfer Rate	18Gbps
Insertion Rating	Connectors rated beyond 10,000 insertions
MTBF	Connectors rated beyond 10,000 insertions
Audio Specifications	HDMI - 32 Channel Audio
Maximum Digital Resolutions	4K 60Hz 1440p 144Hz 1080p 240Hz

Hardware

Active or Passive Adapter	Passive
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	VW-1

**Packaging &
In-the-Box**

Included in Package	1 - 3m HDMI 2.0 Cable
Package Width	8.7 in [22 cm]
Package Depth	7.9 in [20 cm]
Package Height	1.0 in [25 mm]
Shipping (Package) Weight	4.9 oz [138 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	HDMI
Connector 2 (Quantity)	1
Connector 2	HDMI

****Product appearance and specifications are subject to change without notice.***