

10ft (3m) High Speed HDMI Cable with Gripping Connectors, 4K 60Hz/1440p 144Hz, HDR10/HDCP 2.2/ARC, 18Gbps, UHD HDMI Cord for TV/Monitor/Display, TPE Jacket

Product ID: HDMI2-CABLE-GRIP-10F



Connect to a 4K UHD TV or monitor, using this High Speed HDMI Cable. The connector markings enable quick visual identification, distinguishing this cable from other similar-looking or unmarked HDMI cables. Eliminate guesswork and always choose the appropriate cable to support full HDMI 2.0 capabilities.

The HDMI UHD Cord features gold-plated gripping connectors to prevent accidental disconnections. The connectors attach securely to HDMI device ports, making this cable ideal for critical A/V setups such as security systems and HDMI switches.

The HDMI Monitor Cable features a flexible TPE outer jacket that is tested to withstand 2,000 bending cycles at ± 60 degrees, and routes easily around corners and desk edges. Robust strain reliefs enable convenient positioning of the cable. The durable Gold-plated connectors are rated to operate beyond 10,000 insertions.

This High Speed HDMI Cable supports full HDMI 2.0 features:

- Resolutions up to 4K 60Hz using a compatible HDMI source and display
- Supports high refresh rates including 1440p 144Hz and 1080p 240Hz
- 21:9 Aspect Ratio support for cinematic viewing experiences
- High Dynamic Range (HDR10) for higher contrast ratio and vibrant picture quality
- High-Bandwidth Digital Content Protection (HDCP) 2.2 for a secure connection between source and display
- Audio Return Channel (ARC) for sending audio from the TV back to an AV receiver or soundbar
- Up to 32 Uncompressed Digital Audio Channels
- HDMI Ethernet Channel (HEC) for network connectivity over HDMI

- Backward compatible with previous HDMI versions

This HDMI 2.0 Cable is constructed with braided aluminum mylar shielding to minimize EMI for clear, consistent audio/video output and long-term reliable performance.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

Features

- **HIGH PERFORMANCE:** High Speed HDMI Cable is designed for UHD-enabled HDMI devices; Choose the right HDMI cable at-a-glance with performance markings on connectors for quick and easy identification; Up to 18Gbps for seamless 4K 60Hz video
- **GRIPPING HDMI CONNECTORS:** This HDMI 2.0 cord features gold plated gripping male connectors to prevent accidental disconnection due to tension or vibration; Keeps cable securely connected to mounted HDMI displays and hard-to-access HDMI ports
- **QUALITY CONSTRUCTION:** Gold-plated connectors rated beyond 10,000 insertions; Durable TPE Jacket and strain reliefs are halogen-free and RoHS compliant; Tested to withstand 2,000 bending cycles at +/-60 degrees; Braided shield for enhanced EMI protection
- **APPLICATIONS:** Ideal for 4K UHD displays; Up to 144Hz refresh rate at 1440p resolution; Suitable for high performance GPUs and workstations; Connect an HDMI monitor to a 4K docking station
- **SPECS:** Black; 10-foot (3-meter); High Speed HDMI with Ethernet; HDMI 2.0 supports HDR10/ARC/HDCP 2.2/CEC; 4K 60Hz/1440p 144Hz/1080p 240Hz; 18Gbps; 32-ch Audio; Backward Compatible; 30AWG; 6mm (0.24in) O.D.

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Fire Rating VW-1

Performance

Maximum Data Transfer Rate	18Gbps
Maximum Digital Resolutions	4K 60Hz 1440p 144Hz 1080p 240Hz ,
Audio Specifications	HDMI - 32 Channel Audio
MTBF	Connectors rated beyond 10,000 insertions

Connector(s)

Connector A	1 - HDMI
Connector B	1 - HDMI

Environmental

Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Humidity	10% to 90%

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Material	Santoprene - Thermoplastic Rubber (TPE)
Cable Length	10.0 ft [3.0 m]
Cable OD	0.2 in [6 mm]
Product Length	10.1 ft [3.1 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.5 in [1.3 cm]

	Weight of Product	4.6 oz [130 g]
Packaging Information		
	Package Length	7.6 in [19.2 cm]
	Package Width	7.7 in [19.6 cm]
	Package Height	1.2 in [3.0 cm]
	Shipping (Package) Weight	5.1 oz [144.0 g]
What's in the Box		
	Included in Package	1 - 10ft HDMI 2.0 Cable
Warranty Information		
	Warranty	Lifetime

**Product appearance and specifications are subject to change without notice.*