

10ft (3m) HDMI Cable - 4K High Speed HDMI Cable with Ethernet - 4K 30Hz UHD HDMI Cord - 10.2 Gbps Bandwidth - HDMI 1.4 Video / Display Cable M/M 28AWG - HDCP 1.4 - Black

Produkt-ID: HDMIMM10HS



This High Speed HDMI™ Cable with Ethernet is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more.

#### High Speed HDMI™

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

#### Premium Build Quality

Constructed with 28 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

#### Zertifikate Berichte und Kompatibilität



## Anwendungen

- Quick-connect single HDMI® cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.
- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI® with Ethernet)

## Merkmale

- **DURABLE:** Ultra HD high speed fully molded 4K HDMI cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **HIGH SPEED HDMI CABLE:** 10ft (3.1m) HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz | 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **QUALITY CONSTRUCTION:** This HDMI to HDMI cable has a 28AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid (85% coverage) improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 10 ft (3.1 m) | Black | HDMI 1.4b | HDMI Cord Male to Male | 28 AWG | Gold-plated connectors | PVC Jacket | Shield: Al-Mylar foil w/ 85% Braid | ARC, Deep Color, HDCP 1.4, CEC | YCC601 Color | Supports HDMI 1.4 and earlier

---

### Hardware

|                       |                          |
|-----------------------|--------------------------|
| Garantiebestimmungen  | Lifetime                 |
| Anzahl von Leitern    | 2                        |
| Steckverbinderplatten | Gold                     |
| Typ der               | PVC - Polyvinyl Chloride |

## Kabelummantelung

### Leistung

|                         |                 |
|-------------------------|-----------------|
| Max. Digitalauflösungen | 4K x 2K @ 30 Hz |
|-------------------------|-----------------|

### Steckverbinder

|                  |                     |
|------------------|---------------------|
| Steckverbinder A | 1 - HDMI (19-polig) |
| Steckverbinder B | 1 - HDMI (19-polig) |

### Umgebungsbedingungen

|                    |                               |
|--------------------|-------------------------------|
| Betriebstemperatur | 0°C to 35°C (32°F to 95°F)    |
| Lagertemperatur    | -10°C to 80°C (14°F to 176°F) |
| Feuchtigkeit       | 5%-90% RF (kondensationsfrei) |

### Physische Eigenschaften

|                             |                  |
|-----------------------------|------------------|
| Farbe                       | Schwarz          |
| Steckverbinderart           | Gerade           |
| Drahtstärke                 | 28 AWG           |
| Kabellänge                  | 10.0 ft [3.0 m]  |
| Außendurchmesser des Kabels | 0.3 in [7.3 mm]  |
| Produktlänge                | 10.0 ft [3.0 m]  |
| Produktbreite               | 0.8 in [2.0 cm]  |
| Produkthöhe                 | 0.4 in [1.0 cm]  |
| Produktgewicht              | 8.3 oz [235.0 g] |

### Verpackungsinformationen

|            |                  |
|------------|------------------|
| Paketmenge | 1                |
| Paketlänge | 6.9 in [17.6 cm] |

|                                |                  |
|--------------------------------|------------------|
| Paketbreite                    | 7.8 in [19.7 cm] |
| Pakethöhe                      | 1.2 in [3.1 cm]  |
| Versandgewicht<br>(Verpackung) | 8.6 oz [244.0 g] |

---

#### Verpackungsinhalt

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Im Paket enthalten | 1 - 10ft High Speed HDMI® Cable with Ethernet - HDMI - M/M |
|--------------------|------------------------------------------------------------|

---

#### Garantieinformationen

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.