

3ft Slim HDMI Cable - 4K High Speed HDMI Cable with Ethernet - 4K 30Hz UHD HDMI Cord - 10.2 Gbps Bandwidth - HDMI 1.4 Video / Display Cable 36AWG - HDCP 1.4 - Thin HDMI Cable

Product ID: HDMIMM3HSS



The HDMIMM3HSS 3-foot Slim High Speed HDMI Cable supports advanced capabilities, including Ethernet data inter connectivity with compatible HDMI-capable devices, and features a thin cable design (3.5mm in diameter).

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

StarTech.com High Speed HDMI cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance, and are backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Allows multiple High Speed HDMI-equipped devices to share Internet connection (satellite receivers, DVD players, A/V receivers, High Definition TVs, game consoles and more)
- Connect HDMI-equipped devices like LCD TVs, LCD Projectors, Plasma TVs, HDTVs and DVD Players

Features

- HIGH SPEED HDMI CABLE: 3ft (91cm) Slim HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- SLIM AND DURABLE: Ultra HD slim (0.14"/3.6mm OD) HDMI cable w/ durable PVC jacket & strain relief for high

strength/reliability; Thin HDMI cable w/ a low profile design that reduces bend radius & improves flexibility; Ideal for Commercial environments

- **QUALITY CONSTRUCTION:** 36AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid (85% coverage) improve signal integrity and reliability, providing higher quality video and audio

- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo

- **SPECS:** 3 ft (91 cm) Black HDMI 1.4b HDMI Cord Male to Male 36 AWG Gold-plated connectors PVC Jacket Shield: Al-Mylar foil w/ 85% Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	36 AWG
Cable Length	36.0 in [91.4 cm]



Cable OD	0.1 in [3.6 mm]
Product Length	36.0 in [91.5 cm]
Product Width	0.8 in [20 mm]
Product Height	0.4 in [9.8 mm]
Weight of Product	1.1 oz [32.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	1.4 oz [40.0 g]

What's in the Box

Included in Package	3 ft Slim High Speed HDMI Cable with Ethernet - HDMI -M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***

