

3 ft High Speed HDMI Cable for Panel Mount - F/M

Product ID: HDMIPNLFM3



The HDMIPNLFM3 3ft High Speed HDMI Cable for Panel Mount features an HDMI male connector on one end, and an HDMI panel mount (female) molded connector on the other, providing a well-secured, easy to access HDMI connection on any machine port or faceplate.

Backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Extend your HDMI interface and screw mount it to a panel

Features

- Panel mount connector for embedded installations

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)

Connector(s)



Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Environmental

Operating Temperature	5C - 70C
Storage Temperature	-10C - 80C
Humidity	0-85%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	36.0 in [91.4 cm]
Cable OD	0.3 in [6.5 mm]
Product Length	36.0 in [91.4 cm]
Product Width	0.8 in [20 mm]
Product Height	0.4 in [10 mm]
Weight of Product	2.8 oz [79.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.0 in [0.5 mm]
Shipping (Package) Weight	3.0 oz [84.0 g]

What's in the Box

Included in Package	3 ft Standard HDMI Cable for Panel Mount - F/M
---------------------	--

**Product appearance and specifications are subject to change without notice.*

