

1,8m 180° rotierendes High Speed HDMI Kabel - HDMI - St/St

Produkt-ID: HDMIOTMM6



The HDMIOTMM6 High Speed HDMI® Swivel Cable (6 ft) features two gold plated 180° flexible HDMI connectors, which provide a direct link between HDMI-enabled devices such as Blu-Ray players, HDTVs, DVD Players, stereo receivers and more.

The swiveling/pivoting HDMI connectors offer the ability to adjust your installations in tight/narrow spaces where standard connectors will not fit (e.g. wall-mounted flat panel televisions), without having to bend the cable at sharp angles.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMIOTMM6 6-foot HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connecting your HDMI®-capable TV or Monitor to an audio-video source which incorporates HDMI technology
- Connecting to an HDMI-enabled A/V source with very little space near the connection point

Merkmale

- **HIGH SPEED SWIVEL CABLE:** 6 ft (1.83 m) HDMI 1.4b cable supports 4K (3840x2160p, 24, 25, 30Hz | 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** HDMI Ultra HD cable with pivoting/swiveling/rotating connectors that rotate up to 180°, helping installation in narrow spaces or tight angles such as behind wall mounted TV; Long lasting molded PVC connectors; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** 28AWG wire, corrosion resistant gold-plated connectors, and superior EMI shielding with Al-Mylar foil and braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 6 ft (1.83 m) | Black | HDMI 1.4 | HDMI Male to Male | 28 AWG | PVC Jacket | Shield: Al-Mylar foil with Braid | ARC, Deep Color, HDCP 1.4, CEC, YCC601 Color | Supports HDMI 1.4 and earlier

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	19
Steckverbinderplatten	Gold
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht
Feuerwiderstandssklasse	Ausgelegt gemäß CMG (Mehrzweck) e

Leistung

	Max. Digitalauflösungen	4K x 2K @ 30 Hz
Steckverbinder	Steckverbinder A	1 - HDMI (19-polig)
	Steckverbinder B	1 - HDMI (19-polig)
Physische Eigenschaften	Farbe	Schwarz
	Drahtstärke	28 AWG
	Kabellänge	6.0 ft [1.8 m]
	Außendurchmesser des Kabels	0.3 in [7.3 mm]
	Produktlänge	6.0 ft [1.8 m]
	Produktgewicht	4.3 oz [123 g]
Verpackungsinformationen	Paketmenge	1
	Paketlänge	7.0 in [17.7 cm]
	Paketbreite	4.8 in [12.2 cm]
	Pakethöhe	1.1 in [2.8 cm]
	Versandgewicht (Verpackung)	4.7 oz [134.0 g]
Verpackungsinhalt		
	Im Paket enthalten	1 - 6 ft 180° Rotating High Speed HDMI Cable - HDMI - M/M
Garantieinformationen		
	Warranty	Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.